










THIS DRAWING IS A CONTROLLED DOCUMENT. DWG NO 1583000	USED ON _____												
	TOOL NUMBER  -1 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSUL. ADJ. 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS 				CONTACT DESCRIP.	APPLIC. SPECIF.
								LOOSE PIECE 		STRIP FORM 			
	91500-1 91500-3 91500-4 	0.5 - 0.9 [20-18] 1.2 - 2.1 [16-14]	1.52 - 3.30 [.060 - .130]	YES	NO	4.37 ± 0.38 [.172 ± .015]	1.27 ± 0.05 [.050 ± .002]	350547-[] 350550-[] 350669-[] 350705-[]	350218-[] 350536-[] 350654-[] 350687-[]	770250-[] 770251-[] 770254-[] 770008-[]	770007-[] 770008-[] 770193-[] 770008-[]	Univ. MATE-N-LOK Contacts Univ. MATE-N-LOK 2 Contacts	114-1010 & 114-1011 114-1043
	91506-1 91506-3	1.21 - 2.1 [16-14]					1.60 ± 0.05 [.063 ± .002]	350551-[] 350552-[] 350707-[] 350919-[] 350918-[] 770249-[] 770248-[] 770255-[]	350537-[] 350538-[] 350700-[] 350874-[] 350873-[] 770006-[] 770005-[] 770194-[]	770007-[] 770008-[] 770193-[] 770008-[]	Univ. MATE-N-LOK Contacts Univ. MATE-N-LOK 2 Contacts	114-1010 & 114-1011 114-1043	
	91508-1 91508-3	0.5 - 0.9 [20-18]	3.3 - 5.1 [.130 - .200]	YES	NO	4.37 ± 0.38 [.172 ± .015]	1.24 ± 0.05 [.049 ± .002]	350551-[] 350552-[] 350707-[] 350919-[] 350918-[] 770249-[] 770248-[] 770255-[]	350537-[] 350538-[] 350700-[] 350874-[] 350873-[] 770006-[] 770005-[] 770194-[]	770007-[] 770008-[] 770193-[] 770008-[]	Univ. MATE-N-LOK Contacts Univ. MATE-N-LOK 2 Contacts	114-1010 & 114-1011 114-1043	
	91510-1 91510-3	0.2 - 0.38 [24-22] 0.5 - 0.9 [20-18]	1.02 - 2.54 [.040 - .100]	YES	NO	4.37 ± 0.38 [.172 ± .015]	1.02 ± 0.05 [.040 ± .002]	350689-[] 350690-[] 350706-[] 640347-[]	350570-[] 350561-[] 350699-[] 350851-[]	770252-[] 770253-[] 770009-[] 770010-[]	770009-[] 770010-[]	Univ. MATE-N-LOK Contacts Univ. MATE-N-LOK 2 Contacts	114-1010 & 114-1011 114-1043
	91522-1 91522-3	0.32 - 0.6 [22-20]	1.50 - 2.2 [.059 - .087]	YES	NO	3.45 ± 0.25 [.136 ± .010]	0.79 ± 0.05 [.031 ± .002]	170364-[] 170366-[]	170360-[] 170362-[]	770987-[] 770988-[]	770903-[] 770904-[]	Mini-Univ. MATE-N-LOK Contacts Mini-Univ. MATE-N-LOK 2 Contacts	114-5050 & 114-16017 114-13089
		(1 wire) 0.8-0.9 [18] (2 wire) 0.31-0.38 [22]	(1 wire) 1.54-2.4 [.059-.095] (2 wire) 1.5-1.7 [.059-.067]			(1 wire) 3.45 ± 0.25 [.136 ± .010] (2 wire) 3.7 ± 0.2 [.146 ± .008]	1.04 ± 0.05 [.041 ± .002]	794228-[] 794229-[]	794220-[] 794221-[]				
								770985-[] 770986-[]	770901-[] 770902-[]				
	91529-1 91529-3	0.12 - 0.24 [26-24] 0.32 - 0.38 [22]	1.2 - 1.75 [.047 - .069]	YES	YES	3.45 ± 0.25 [.136 ± .010]	0.69 ± 0.05 [.027 ± .002]	170363-[] 170365-[] 794136-[]	170359-[] 170361-[] 794136-[]	770985-[] 770986-[]	770901-[] 770902-[]	Mini-Univ. MATE-N-LOK Contacts Mini-Univ. MATE-N-LOK 2 Contacts	114-5050 & 114-16017 114-1111 114-13089
	91536-1 91536-3	0.5 - 0.9 [20-18]	2.0 - 3.0 [.079 - .118]	YES	NO	3.45 ± 0.25 [.136 ± .010]	1.07 ± 0.05 [.042 ± .002]	171638-[] 171639-[]	171636-[] 171637-[]	171636-[] 171637-[]	171636-[] 171637-[]	Mini-Univ. MATE-N-LOK Contacts	114-5050 & 114-16017
		(1 wire) 1.2-1.4 [16] (2 wire) 0.5-0.6 [20]	(1 wire) 2.5-3.2 [.098-.126] (2 wire) 2.0-2.4 [.079-.094]			(1 wire) 3.45 ± 0.25 [.136 ± .010] (2 wire) 3.70 ± 0.20 [.146 ± .008]	1.27 ± 0.05 [.050 ± .002]						
	91594-1 91594-3	0.50-0.89 [20-18] 0.50-1.42x2 [16-20x2]	2.00-3.20 [.079-.126] 2.26-3.20 [.098-.126]	YES	NO	(1 wire) 3.45 ± 0.25 [.136 ± .010] (2 wire) 3.70 ± 0.20 [.146 ± .008]	1.07 ± 0.05 [.042 ± .002]	794230-[] 794231-[]	794406-[] 794407-[] 794222-[] 794223-[]	794406-[] 794407-[] 794222-[] 794223-[]	794406-[] 794407-[] 794222-[] 794223-[]	Mini-Univ. MATE-N-LOK 2 Contacts	114-1111

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY. IT IS NOT TO BE DISCLOSED TO ANY OTHER PARTY WITHOUT THE WRITTEN AUTHORIZATION OF TE CONNECTIVITY. ANY VIOLATION OF THIS POLICY WILL BE PROSECUTED TO THE FULL EXTENT OF THE LAW.

 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

2. AMP, CERTI-CRIMP, and MATE-N-LOK are trademarks.

 -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY. -3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.

 SUPERSEDED

 -4 IS A CERTICRIMP II HAND TOOL ASSEMBLY FOR SMALL INSULATION DIAMETER.

6. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.










CERTI-CRIMP II DATA SHEET

DWN	21FEB2012	MATERIAL	-	HEAT TREAT	-
CHK	22FEB2012				
APVD	22FEB2012				
NAME					
CERTI-CRIMP II TOOL DATA SHEET					
UNIVERSAL MATE-N-LOK CONTACT FAMILY					
SCALE	SIZE	DRAWING NO	SHEET	REV	
-	A1	1583000	1	2	D1

0	PLC	±	-
1	PLC	±	-
2	PLC	±	-
3	PLC	±	-
4	PLC	±	-

ANGLES±	-
SURFACE TEXTURE	✓

LOC
A
DIST
00

THIS DRAWING IS A CONTROLLED DOCUMENT. FORM NO 1583000	USED ON _____										
	TOOL NUMBER  -1 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSUL. ADJ. 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS 		CONTACT DESCRIPT.	APPLIC. SPECIF.
								LOOSE PIECE 	STRIP FORM 		
	 91574-1	0.20-0.56 [24-20]	1.52-2.54 [.060-.100]	YES	NO 	5.16 ± 0.38 [.203 ± .015]	1.05 ± 0.08 [.041 ± .003]	350689-[]	350570-[]	Universal MATE-N-LOK Contacts	114-1010 & 114-1011
		0.75-0.89 [18]					1.27 ± 0.08 [.050 ± .003]	350690-[] 350706-[]	350561-[] 350699-[]		
	 91575-1 91575-3	0.50-0.89 [20-18]	2.54-3.31 [.100-.130]	YES	NO 	5.16 ± 0.38 [.203 ± .015]	1.29-1.45 [.051-.057]	350547-[] 350705-[]	350218-[] 350687-[]	Universal MATE-N-LOK Contacts	114-1010 & 114-1011
0.75+0.75 OR 0.75+1.25 [18+18 OR 18+16]		1.60-1.75 [.063-.069]					350669-[] 350550-[]	350564-[] 350536-[]			
1976176-1	18 GA SOLID	1.02-2.54 [.040-.100]	YES	NO 	4.37-0.38 [.172-.015]	1.118 ± .025 [.044 ± .001]	350689-[] 350550-[] 350690-[] 350547-[]	350851-[] 350536-[] 350561-[] 350218-[]	Universal MATE-N-LOK Contacts	114-1010 & 114-1011	

 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

2. AMP, CERTI-CRIMP, and MATE-N-LOK are trademarks.


 -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY.
-3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.

 SUPERSEDED

 -4 IS A CERTICRIMP II HAND TOOL ASSEMBLY FOR SMALL INSULATION DIAMETER.

6. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN: 21FEB2012	MATERIAL: -	HEAT TREAT: -
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± -		CHK: 22FEB2012	 TE Connectivity	
APVD: 22FEB2012		NAME: B.A. WOLFE		CERTI-CRIMP II TOOL DATA SHEET UNIVERSAL MATE-N-LOK CONTACT FAMILY		
SCALE: -		SIZE: A1		DRAWING NO: 1583000		SHEET 2 of 2
SURFACE TEXTURE: 		REV: D1				

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY. IT IS TO BE USED ONLY FOR THE PURPOSES AND APPLICATIONS SPECIFIED IN THE DRAWING. IT IS NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, WITHOUT AUTHORIZATION FROM TE CONNECTIVITY.

LOC
A
DIST
00