





ROHS Compliant

Code: FF24C2



NOTES:

ELECTRICAL:

1. VOLTAGE RATING : 125 VAC
2. CURRENT RATING : 1.5 AMP
3. CONTACT RESISTANCE : 100 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN. @ 500 VDC
5. DIELECTRIC STRENGTH : 750 VAC 60Hz, 1MIN.

MECHANICAL:

1. HOUSING MATERIAL : ABS UL94V-0
2. PANEL FRAME : CARBON STEEL, POWDER COATING IN BLACK COLOR
3. IDC MATERIAL : PC UL94V-0
4. CONTACT MATERIAL : PHOSPHOR BRONZE STAMP PIN t=0.35 mm
Min.50 micro-inch Gold plating over 50-80 micro-inch Nickel plated
5. IDC CONTACT : PHOSPHOR BRONZE WITH NICKEL PLATING

ENVIRONMENTAL:

1. STORAGE : -40°C TO +85°C
2. OPERATION : 0°C TO 70°C

CONFORMING TO TIA 568.2-D

MATES WITH MODULAR PLUG CONFORMING TO TIA-1096-A.

CAT.5e