




COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
1	DIS-C-000585	T.K	E.K	07.07.27					



DIP POST LOCATION DIMENSIONS IN THE VIEW FROM CONNECTOR OPENING SIDE
(RECOMMENDED MAXIMUM PANEL THICKNESS : 1.2)



PANEL INSTALLATION HOLE
PANEL THICKNESS(0.7~2)



- NOTES
- FINISH OF REF.NO. ②
CONTACT AREA : GOLD 0.2μ m min.
DIP AREA : GOLD FLASH.
UNDER PLATING: NICKEL 2μ m min.
 - RECOMMENDED TIGHTENING TORQUE OF REF.NO. ⑥ : 0.8 N·m.
LOOSENED NUT MAY CAUSE THE DETERIORATION OF WATER-RESISTANCY.
THE USE OF LOOSENING-PREVENTIVE ADHESIVE IS STRONGLY RECOMMENDED.
RECOMMENDED THREAD LOCKER : LOCTITE 271, LOCKPRIMER 7649, HENKEL JAPAN LTD.
 - AFTER REF.NO. ④ IS INSERTED TO REF.NO. ①, REF.NO. ① IS MOUNTED ON THE PANEL.
MAKE SURE THAT REF.NO. ④ DOES NOT HAVE ANY FACTORS TO REDUCE WATER-RESISTANCY, SUCH AS SCRATCH, TWIST, PINCHING, OR DUST.

3	PPS	(BLACK) UL94V-0	6	BRASS	NICKEL PLATING
2	COPPER ALLOY	1	5	PHOSPHOR BRONZE	NICKEL PLATING
1	PPS	(BLACK) UL94V-0	4	CR	(BLACK)
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
CODE NO. (OLD) CL	DRAWN T.HORII		DESIGNED H.NAGANO	CHECKED E.KUNII	APPROVED M.SATO
	'06 3 3		'06 3 7	'06 3 8	'06 3 8
SCALE 5 : 1	DRAWING NO. EDC3-113454-71		PART NO. HR30-7R-12PD(71)		
UNITS mm	HRS HIROSE ELECTRIC CO., LTD		CODE NO. CL130-1017-9-71		

TO
R