






2366036-1 SHOWN AS



DELIVERY CONDITION
LEVER IN LOCKED POSITION

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL RELEASE DRAWING	15JAN2020	S.ZH	I.Y
A1		REVISE	15JAN2021	S.Z	I.Y
B		REVISED PER PCN JE-21-004518	16APR2021	S.Z	Z.Z



REFERENCE VIEW FOR PLUG HSG ASSEMBLY WITH
SECOND LOCK IN END-LOCK AND LEVER IN PRE-LOCKED POSITION


NOTES:

- 1 ASSEMBLY PN AND PART REVISION:
2366036-X A
X: X=1, 2, 3, 4 FOR VARIOUS CODE.
A: PART REVISION. DETAIL SEE TABLE ON THE DRAWING SHEET 1.
2. MATERIAL: SEE TABLE ON THE DRAWING SHEET 1.
- 3 IDENTIFICATION FOR CABLE PINOUT.
- 4 THE ASSEMBLY DATE CODE: IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY.
SUCH AS :19A1309
19: YEAR, FIRST AND SECOND DIGITS (19=2019)
A: MONTH, THIRD DIGIT , EXCLUDING "1" , A=JAN, B=FEB, C=MARCH...H=AUGUST,J=SEPTEMBER...
13: DAY, FOURTH AND FIFTH DIGITS(13=13th DAY)
09: HOUR, SIXTH AND SEVENTH DIGITS(09=09AM)
5. INSTALL LEVER AND SECOND LOCK ONTO HOUSING AS SHOWN.
6. VERIFY THE SECOND LOCK SEATED ON PRE-LOCK POSITION FOR DELIVERY.
PULL SECOND LOCK TO PRE-LOCK BEFORE TERMINAL INSERTION IN CASE OF SECOND LOCK BEING HIT TO END-LOCK POSITION.
7. APPLICABLE TERMINAL PART NUMBERS AND WIRE SIZE SHOWN AS BELOW FOR RECOMMEND.
CONSULT TE CONNECTIVITY FOR MORE APPLICATION INFORMATION.


7-1452656-1	TIN	0.75	Ø 1.40~Ø 1.90
7-1452659-1	TIN	1.0~1.5	Ø 1.90~Ø 2.40
TERMINAL PN	TERMINAL PLATING	WIRE SIZE (MM2)	INSULATION WIRES OD (MM)

8. THIS PLUG MATES WITH TAB 2366066-X. (X=1, 2, 3, 4 FOR VARIOUS CODE).


CODING A
2366036-1








CODING B
2366036-2



CODING C
2366036-3



CODING D
2366036-4



1	1	1	1	LEVER	PA66-GF30	YELLOW	3
1	1	1	1	SECOND LOCK	PBT-GF30	YELLOW	2
1				HOUSING, CODE D	PBT-GF30	BLUE	1
	1			HOUSING, CODE C	PBT-GF30	GREEN	
		1		HOUSING, CODE B	PBT-GF30	GRAY	
			1	HOUSING, CODE A	PBT-GF30	BLACK	
-4	-3	-2	-1	PART NO	MATERIAL	COLOUR	ITEM NO
D	C	B	A	CODING			
B	B	B	B	REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)			
19.41	19.41	19.41	19.41	WEIGHT OF EACH ASSY NO. [g]			
QTY REQD PER ASSY				PARTS LIST			
THIS DRAWING IS A CONTROLLED DOCUMENT. OTHERWISE SPECIFIED:				DWN S.ZHANG	03JAN2020	TE Connectivity	
				CHK E.JIANG	03JAN2020		
				APVD I.YIN	03JAN2020		
				PRODUCT SPEC 108-32618			
DIMENSIONS: mm				TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 48POS. MCON 1.2LL, PLUG HSG ASSY UNSEALED, CONNECTOR	
				0 PLC ±0.5 1 PLC ±0.3 2 PLC ±0.20 3 PLC ±0.100 4 PLC ±0.0500 ANGLES ±5°		APPLICATION SPEC 116-32365	
				FINISH		SIZE A	
MATERIAL				WEIGHT		CAGE CODE 00779	
-				-		DRAWING NO C=2366036	
-				RESTRICTED CUSTOMER		RESTRICTED TO REV B	
				SCALE 2:1		SHEET 1 OF 1	