


**Notes:**

1. Only RoHS Compliant Processes and Materials used for this assembly.
2. Cable Weave to BLACK base and ORANGE strip
3. Marking to be on Silver Label's covered with Clear Heat Shrink
4. Sweep Tested for DC to 50GHz, Plot Data and Store.
5. Serial No. to be Marked as Cxxxxx, where xxxxx = sequential no. from log.
6. BLUE Caps to be Fitted Prior to Packaging
7. Cables to be Coiled and Placed in Electrostatic Bag with ConductRF Plotted Data & Label.


## Site-Flex Phase Stable Rugged RF Test Cable



L	XXX	Max Insertion Loss(dB)	
		40GHz	50GHz
2ft	F02	3.29	3.73
4ft	F04	6.21	7.04
L	XXX	40GHz	50GHz
0.5M	0M5	2.77	3.14
1M	1M0	5.16	5.85
VSWR (Max)		1.30:1	

Part No. Configurator - XXX

FXX = Length in Feet (eg F03=3ft)  
 SXX = Length in Inches (eg S18=18")  
 XMX = Length in Meters (eg 2M5=2.5m)  
 CXX = Length in CM (eg C50=50cm)

					Customer DWG	Title: <b>Site-Flex 50GHz - 2.4mm Female to 2.4mm Female</b>				
						Remarks:	Originated: 08/03/15	Conduct RF sales@ConductRF.com Tel: +1 978 374 6840	Range: SF	
2	Adjusted Marking & Shell		DG	11/09/16	Dwg Ref: SW50G-CFCF					
1	Pre-Release		DG	10/18/16						
REV.	DESCRIPTION	ECN	DRAWN	DATE	Tolerances: Length +/-2%	Checked: JW	Approved: PL	Rev: 2	Part No: <b>SW50G-CFCF-XXX</b>	
REVISION HISTORY										