









ISS.	AMEND	DATE
1	1st DRAWN	23/07/14
2	UPDATED	13/08/21



M8xP0.75
ALL NUTS SUPPLIED
UNASSEMBLED,
BULK PACKED.

SPECIFICATIONS

Contact Resistance: 30mΩ max
 Insulation Resistance: 100MΩ min at DC 500V
 Dielectric Withstanding Voltage: AC 500V for 1 minute
 Tolerance: ±0.30 unless otherwise specified



ITEM	DESCRIPTION	MATERIAL	FINISH	QTY
1	SLEEVE CONTACT	PHOSPHOR BRONZE	SILVER	1
2	RING CONTACT	PHOSPHOR BRONZE	SILVER	1
3	TIP CONTACT	PHOSPHOR BRONZE	SILVER	1
4	BREAK CONTACT	BRONZE	SILVER	1
5	RING NUT	BRASS	NICKEL	1
6	HOUSING	PBT	BLACK	1

RoHS
COMPLIANT

TOLERANCE
 NO DEC. PLACE ±
 1 DEC. PLACE ±
 2 DEC. PLACE ±
 HOLE Ø ±
 ANGLES ±
 UNLESS OTHERWISE STATED

Cliff Electronic Components Ltd.

76 Holmetherpe Avenue, Holmetherpe Industrial Estate,
 Redhill, Surrey, RH1 2PF, England, UK
 Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

ANGLE PROJECTION:

DO NOT SCALE

MATERIAL: SEE TABLE

FINISH: CLEAN

TITLE: 3.5mm VERTICAL JACK ST WITH NUT

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2014

DRAWN: T.J.O.

APPROVED: D.P.J.

DRWG. No. **FC681374V**

FORM: A4DRWGH