





155.	AMENU	DAIL
1 2 3	1st DRAWN ADD M3 VARIANT CLIP VIEW CORRECTED	12/05/201 29/05/201 26/06/201

Material:

Insert: ABS

2. Frame: Nickel plated zinc diecast

3. Shell: Nickel plated steel

Contacts: Gold Plated

Notes:

-2.8

-2.3

Voltage rating: 30V AC 1.


2. Current rating: 1.8 A max


3. Contact resistance: 50mΩ max Insulation resistance: 20MΩ min 4.

5. Dielectric withstanding voltage: 500V AC

Operating Temperature: -20°C to 50°C 6.

VARIANTS			
PART No.	HOLE DETAILS		
CP30210NM	HOLE Ø3.50 x CSK 82° x Ø5.85		
CP30210NM3	M3 HOLES		





RoHS/ **▼**COMPLIANT

TOLERANCE

NO DEC. PLACE ±

1 DEC. PLACE ±

2 DEC. PLACE ±

HOLE Ø ±

ANGLES ±

UNLESS OTHERWISE STATED

Cliff Electronic Components Ltd.
76 Holmethorpe Avenue, Holmethorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.ul

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2016

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

3rd ANGLE PROJECTION: ()

DO NOT SCALE

See Notes MATERIAL: TITLE: FT METAL USB 3.0 A to USB 3.0 B See Notes FINISH: DRWG. No. DRAWN: T.J.O. APPROVED: D.P.J.

CP30210NM

FORM: A4DRWGI