


USB2.0 AM TO CM CABLE L=1.0M




1. test conditions:

- 1.100% of short circuit, open circuit test & dislocation.
2. Insulation impedance:10M ohm(MIN) DC 300V.
3. Conduction impedance:2 ohm(MAX).
4. Withstand voltage test:DC 300V/10ms

2. processing instructions:

1. C Type end was peeled 10 ~ 15 mm, outside order, in accordance with the thread gauge to conductor LiRu fixture groove (ground to twist In the GND PIN) weaving take 2 ~ 3 shares of twist in the Shell welding Pad, pay attention to the tin point should not be too large.
2. USB AM end and ground wire woven take 2 ~ 3 shares of twisting the welding on the GND Pad (lap plus tin soldering iron shell), pay attention to Tin not too big.
3. The P1 end after good conductor welding the PCB must be UV glue, UV glue dozen thin as far as possible,

4、Pin Assignment:



⑨	A0040411-00002	Low pressure molding compound, transparent color, hardness, 40 ~ 48 d	1	g
⑧	A0020100-00173	USB TYPE C~The tin plating nickel	1	pcs
⑦	A0020100-00172	USB TYPE C~On the tin plating nickel	1	pcs
⑥	A10-R075552	Heat shrinkable casing~ ϕ 1.0mm~black	0.016	M
⑤	A5-R047107	45P WHITE PVC ROHS	16	g
④	A5-R047011	transparent PE ROHS LDPE	3	g
③	B010-00870	TYPE C-Type Connector With empty PCB+SMT	1	pcs
②	A2-R029107	USB AM L=18.10MM WHITE INSULATION SHELL PLATED:NICKEL	1	pcs
①	A4-R005014	NO-UL 30AWG (19/0.06TC)*2C+24AWG (26/0.1TC+250Dnylon)+3E (19/0.05TC+250Dnylon)+AB (16/9/0.06TC 95%TC) OD:3.0MM WHITE PVC NO MARKING	0.5	M
NO		DESCRIPTION	Q'TY	UNIT

REV	ECN	DESCRIPTION		DATE	NAME	
	TOLERANCE INCHES M/M		TITLE: USB 2.0 AM TO CM L=0.5M			
	.X	.015				.30
	.XX	.010				.10
	.XXX	.005				.05
DRAWN BY		zhouwenlong	CUSTOMER :	CPC		
			CUSTOMER P/N :	PSG91485		
CHECK BY			SCALE	NONE	DRAWING NO.:	REV
			UNIT	mm		A01
APPD BY			DATE	2017.05.03	C06026-00268	1/2