



Datenblatt - Fiche technique - Data sheet


11.02.8765









USB 2.0 Kabel, reversibel, A - Micro B, ST/ST, schwarz, 1,0 m

Câble USB 2.0, reversible, A - Micro B, M/M, noir, 1,0 m

USB 2.0 Cable, reversible, A - Micro B, M/M, black, 1.0 m



1000±30mm



Electrical Test:

1. 100%Test(Open, short ,miss wire)
2. Contact Resistance: 2 ohm max.
3. Insulation Resistance: 3M ohm min.
4. Hi-pot:300V DC/10ms

NOTE:

1. USB 2.0 Cable 28AWG*2C+26AWG*2C+Jacket OD:2.0*5.5mm Color: Black
- 2.USB(A) M Solder Type Shell Nickel Insulation: White
- 3.Micro USB(B) M Solder Type Shell Nickel Insulation: Black
- 4.INSIDE MOLDING:PE
- 5.OUTSIDE MOLDING:Black TPE

Pin Assignment

Conn.1	Conn.2
1	1
2	2
3	3
4	5

REV.	DATE	CONTENTS OF CHANGE	DESIGNER	TOL ±								APPROVAL	CHECK	DRAWING	DESIGN	DRAWING NAME					
				RANGE	Pla	Met	Ins	Por	Cab	Pac	Gas					DIS	DATE	ROLINE Reversible USB 2.0 Cable	A-Micro B, M/M, 1m, black		
△				0~6	0.1	0.1	0.1	0.2	0.5	1	0.5	0.2	PHILIP	PHILIP	HENRY	2015-12-17	PART NO.	11.02.8765	ROO		
△				6~30	0.1	0.1	.15	.25	1	1	0.5	.25									
△				30~80	0.1	.15	0.2	0.3	2	1.5	1	0.3									
△				80~180	.15	.15	.25	0.3	2	2	1	.45									
△				180~315	.15	0.2	0.3	0.4	2.5	2	1	0.6									
△				315~800	0.2	0.3	0.4	0.5	3	3	2	1.1	SCALE	1:1	UNIT	MM					