






CAT. LISTING	ISSUE NO.	OPERATING TEMPERATURE	SUPPLY		HOUSING MATERIAL	SENSING RANGE		OUTPUT NOMINAL	MAXIMUM COIL RESISTANCE AT 70° C	NUMBER OF TURNS
						NOMINAL	MAXIMUM			
CSNA111	2	0° C TO +70° C	+15V	-15V	POLYCARBONATE/ABS BLEND	50A	70A	± 50mA	90 Ohms	1000 ± 1
CSNC241	1	-25° C TO +85° C	+13V	-13V	POLYCARBONATE/ABS BLEND	50A	90A	± 50mA	50 Ohms	1000 ± 1
CSNB131	1	0° C TO +70° C	+15V	-15V	POLYCARBONATE/ABS BLEND	50A	100A	± 25mA	130 Ohms	2000 ± 1
CSNB121	1	0° C TO +70° C	+15V	-15V	POLYCARBONATE/ABS BLEND	50A	100A	± 25mA	160 Ohms	2000 ± 1
CSND341	1	0° C TO +70° C	+5V	-5V	POLYCARBONATE/ABS BLEND	15A	25A	± 15mA	50 Ohms	1000 ± 1
CSNA111-040	1	-40° C TO +85° C	+15V	-15V	POLYCARBONATE/ABS BLEND	50A	70A	± 50mA	90 Ohms	1000 ± 1
CSNN191	1	0° C TO +70° C	+15V	-15V	POLYCARBONATE/ABS BLEND	10A	15A	± 50mA	20 Ohms	200 ± 1

CSN SERIES CHART I
MTG-CSN-01
 REPLACES

 DRAWING NUMBER
 ISSUE 9/10
 RELEASE No.



NOTES :-
 1. MOUNTING HOLES 0.95 DIA.
 2. INK COLOUR GREY.



REVISED	DATE	BY	REASON
4			
5	5.90		
6			
7	2-91		
8	6/91		
9	11/94		
10	11/95		

DRAWN I WEIR 5/89
 CHECK
 DESIGN
 AUTHOR *N

THE COPYRIGHT OF THIS DRAWING IS THE PROPERTY OF HONEYWELL LTD. THE DRAWING IS SUPPLIED IN CONFIDENCE AND MUST NOT BE USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS SUPPLIED.

THIRD ANGLE PROJECTION

SCALE :- 2/1

DIMENSIONS ARE IN MILLIMETRES

MODIFY ON CAD3D SYSTEM ONLY