


Für diese Unterlage behalten wir uns alle Rechte vor, auch für den Fall der Patentierung oder Gebrauchsmusteranmeldung. Sie darf ohne unsere vorherige schriftliche Zustimmung weder vervielfältigt noch sonstwie benutzt, noch Dritten zugänglich gemacht werden.

Nur rol gestempelte oder auf Laufrunde gedruckte Dokumente unterliegen dem Änderungsdienst und sind zur Fertigung freigegeben. Only red stamped or on potcard printed documents are managed. These documents are approved for production.


All Rights reserved, including possible patents or trademarks. Documents shall not be provided to a third party or duplicated in any form without prior written permission.

CAD: Creo Parametric


Additional coding
View in direction B
5:2



S1TBAT0-H005PN-0000
Part-ID: 50295315
Mechanical coding: B
Color coding: red




S1TCTA0-H005PN-0000
Part-ID: 50295316
Mechanical coding: C
Color coding: blue





S1TDAT0-H005PN-0000
Part-ID: 50295317
Mechanical coding: D
Color coding: green


Only insert
View in direction A
4:1



Keying indication
Color coding



S1TAAT0-H005PN-0000
Part-ID: 50295314
Mechanical coding: A
Color coding: light brown



Delivery condition
1:1

Technical information:


- Current load: 13A (with AWG16) acc. to SAE-AS39029D
- Rated voltage: <50 V AC / <75 V DC (SELV acc. IEC 61140:2016) 1)
- Test voltage: 1800 V AC (acc. EIA-364-20F:2019, sea level)
- For technical information, materials and surfaces see datasheet D00016301
- For useable accessories see datasheet D00016302
- For an assembly instruction see datasheet D00016303

1) In case that other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid.

2) For further contact information and crimping instructions see datasheet D00016300

All datasheets available at www.odu.de

Bei den hier dargestellten ODU-Steckverbindern handelt es sich nach DIN EN 61984:2009 um Steckverbinder ohne Schaltleistung (COC) !
/the pictured ODU-connectors are in relation to DIN EN 61984:2009 connectors without switching capacity (COC) !



Contact	Material-ID	Wire size
#16	50267258	AWG 16-20

 Allgemeintoleranz/general tol.: DIN ISO 2768-mH Tolerierung / Tolerancing: DIN ISO 8015		Benennung/description: Push-Pull Plug AMC Series T		Werkstoff: material: see BOM
		Zeichnungs-Nr.: Drawing-Id.: 00191404		Maßstab: scale: 3:1
Status/state: Approved	Version: revision: -	Material-Nr.: Material-Id.: S1T_AT0-H005PN-0000		Format: size: A3
Erstellt/prepared 09.11.2020 fheitzinger	Geaendert/revised 09.11.2020 fheitzinger	ODU-Nr.: ODU-Id.: S1T_AT0-H005PN-0000		Einheit: dim.: mm
Freigabe/released 22.04.2021 chobmaier	ODU-MUEHLDORF Datum/date	Ursprung/origin.: S1T_AT0-H005PN-0000		Bl.: sheet: 1
Name/name				