



**1-CONDUCTOR PCB TERMINAL  
STRIP 1 SOLDER PIN / POLE  
STAGGERED PIN SPACING 3.5 MM / 0.  
138 IN WITH PUSH BUTTONS  
250-202 TO 250-224**

<b>ITEM-NO. (ITEM-NO.)</b>	250-206
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.2 - 1.5
<b>Cross section2 (Cross section / AWG)</b>	24 - 16
<b>Strip length (Strip length / mm)</b>	8.5 - 9.5
<b>Measured voltage (Measured voltage / V)</b>	320
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	8
<b>RM (PIN SPACING / mm)</b>	3.5
<b>P (NO. OF POLES)</b>	6
<b>Height (Height / mm)</b>	13.1
<b>Width (Width / mm)</b>	22.5
<b>Depth (Depth / mm)</b>	12
<b>No. of connection Points (No. of connection Points)</b>	6
<b>No. of potentials (No. of potentials)</b>	6
<b>COLOR (COLOR)</b>	grau
<b>WEIGHT (WEIGHT / g)</b>	2.94
<b>Comment (Comment)</b>	L = (No. of poles x Pin Spacing) + 1.5 mm
<b>Dimensions (Dimensions)</b>	1 +0.1 mm