



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	19JAN2022	SCB	PS

2:1



2385010-3 AS SHOWN

7.62 ±0.1 $\triangle 5$



NOTES:

- $\triangle 1$ MATERIALS & FINISH
HOUSING : PA66, UL94 V0, COLOR - LIGHT GREEN
PUSH BUTTON : PA66, UL94 V0, COLOR - ORANGE
CONTACT : COPPER ALLOY, TIN PLATED
SPRING : STAINLESS STEEL



2. MECHANICAL
WIRE STRIPPING LENGTH : 11 - 12 mm


3. ELECTRICAL
WIRE RANGE : 12 - 26 AWG
RATED CURRENT AND VOLTAGE : 20AMP 300V (UG B/C)
: 5AMP 600V (UG D)
INSULATION RESISTANCE : >2000 M Ohm (500V DC)

4. OPERATING TEMPERATURE RANGE : -40°C TO +105°C

- $\triangle 5$ TOLERANCE NOT CUMULATIVE

89.52	12	1-2385010-2
81.90	11	1-2385010-1
74.28	10	1-2385010-0
66.66	9	2385010-9
59.04	8	2385010-8
51.42	7	2385010-7
43.80	6	2385010-6
36.18	5	2385010-5
28.56	4	2385010-4
20.94	3	2385010-3
13.32	2	2385010-2
DIM A	POS	TE PN



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24 JAN 2022 SHRICHARANA B	 TE Connectivity		
		CHK 24 JAN 2022 SUBHASREE S			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 24 JAN 2022 PRASHANTH S	NAME TERMINAL BLOCK, SPRING PLUG, 7.62 mm PITCH		
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	PRODUCT SPEC 108-32299	SIZE A 3		
		APPLICATION SPEC 114-32242			
MATERIAL 	FINISH 	WEIGHT -	DRAWING NO C-2385010		
CUSTOMER DRAWING					
			SCALE 3:1		
			REV A		