
		REVISIONS			
REV	ECO	DESCRIPTION DATE BY			
A1	-	RELEASE NEW DRAWING	04/JAN/22	IAN	TOMMY



NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

SHELL: ZINC ALLOY, NICKEL PLATED COUPLING RING: ALUMINUM ALLOY, ANODIZE INSERT AND RETAINING RING: THERMOPLASTIC SEAL: SILICONE RUBBER

2. MODIFICATIONS: THREADED HOUSING;

3. SPECIFICATIONS:

- 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
- 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.

NORMAL DIA. WIRE SEAL;

- 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
- 3.4 MOISTURE RESISTANCE:

IP68(IM OF WATER FOR A PERIOD OF 24 HOURS,MATED CONDITION);

- IP69K(MATED CONDITION).
- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDBM04-24-91P* (* = SEAL TYPE)
- 5. BREAKAWAY FUNCTION OCCURS AT AN AXIAL LOAD OF 50 LBS TO 100 LBS.

6. CONTACTS 4 AND 5 ARE INTERNALLY CONNECTED. (BUILT - IN BRIDGE)


7. CAVITY 5 IS WITH CONTACT SIZE 16 AND THE GROMMENT IS SEAL


8. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

9 CONTACT SIZE AND WIRE RANGE:

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL WIRE	CURRENT
SIZE	O.D.	O.D.	RANGE	RATING
0	4.83 mm	6.10 mm	8-10AWG	COAMDO
8	(.190 in)	(.240 in)	(10.0-5.0mm²)	60AMPS
12	3.40 mm	4.32 mm	10-14AWG	25AMPS
12	(.134 in)	(.170 in)	(6.0-2.0mm ²)	ZUAIVIPU
40	2.54mm	3.40 mm	14-20AWG	4241400
16	(.100 in)	(.134 in)	(2.0-0.5mm ²)	13AMPS

10. MEET THE DIMENSION OF IMPLEMENT BUS BREAKAWAY CONNECTOR OF ISO 11783-2.





	AHDBMO)6-24-918	SN		REF:HDB36-24-91SN				ĺ	
QUANTITY	PART N	RT NUMBER			DESCRIPTION			ITEM		
		7	MAT	ERI	٩LS) LI	ST			
		DATE		Λ	mnha					
1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 Fractions ±1/64		mphe)						
2 PL DEC ±0.15 3 PL DEC ±0.08	Angles ±1°	CHECKED:	SULLEN	04/JAN/22	Sine Systems - www.amphenol-sine.com		_			
3) Note reference	- ×	ENGINEER:			44724 Morley Drive					
MATERIAL SPECIFICA	TIONS:	APPROVAL:	TOMMY	05/JAN/22			Clinton Township, MI 48	J36		
		CUSTOMER:				- ,	UG,SOCKET,24SZ	, -		,
			S IS SUPPLIED I		BA'	YONE	T COUPLING,DUR	AMATE A	HDB	М
PROCESS SPECIFICATIONS: INFORMATION ONLY, DESIGN FEATURE SPECIFICATIONS AND PERFORMANCE SHOWN HEREON ARE THE PROPERTY THE AMPHENOL CORPORATION. NO RI OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SILBJECT TO NORMA		RMANCE DATA ROPERTY OF DN. NO RIGHTS LIED. ALL O NORMAI	B	C-	AHDBM06-2	4-91SN		41		
NEXT ASS'Y:			ING VARIATION	S.	SCALE: N	ONE	DURAMATE	sнеет 1	OF	1

ATEAHDBM DWG NO: AHDBM06-24-91SN

AT ST.

AT Series™ - Contact Size 16 Options

	Machined Contacts, Sockets & Pins				
Part Number	Description	Size	AWG	Туре	
AT60-215-1631	Male Contact - Pin, Gold-plated	16	14	Machined	
AT62-209-1631	Female Contact - Socket, Gold-plated	16	14	Machined	
AT60-215-16141	Male Contact - Pin, Nickel-plated	16	14	Machined	
AT62-209-16141	Female Contact - Socket, Nickel-plated	16	14	Machined	
AT60-202-1631	Male Contact - Pin, Gold-plated	16	16-20	Machined	
AT62-201-1631	Female Contact - Socket, Gold-plated	16	16-20	Machined	
AT60-202-16141	Male Contact - Pin, Nickel-plated	16	16-20	Machined	
AT62-201-16141	Female Contact - Socket, Nickel-plated	16	16-20	Machined	
AT60-202-1631-22	Male Contact - Pin, Gold-plated	16	22-24	Machined	
AT62-201-1631-22	Female Contact - Socket, Gold-plated	16	22-24	Machined	
AT60-202-16141-22	Male Contact - Pin, Nickel-plated	16	22-24	Machined	
AT62-201-16141-22	Female Contact - Socket, Nickel-plated	16	22-24	Machined	

Tooling - Machined Contacts				
Part	Part Number	Description		
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)		
3	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)		

	Contact Removal Tools				
Part	Part Number	Description			
3	ATRT-100	Used for removal of contacts for A Series™ products			
	AT11-310-1605	Contact Removal Tool, Plastic, Size 16			
	A114017	Sealing Plug, Size 16, White			

	Stamped & Formed Contacts, Sockets & Pins				
Part Number	Description	Size	AWG	Туре	
AT60-14-0144	Male Contact - Pin, Gold-plated	16	14-16	Stamped & Formed	
AT62-14-0144	Female Contact - Socket, Gold-plated	16	14-16	Stamped & Formed	
AT60-14-0122	Male Contact - Pin, Nickel-plated	16	14-16	Stamped & Formed	
AT62-14-0122	Female Contact - Socket, Nickel-plated	16	14-16	Stamped & Formed	
AT60-16-0144	Male Contact - Pin, Gold-plated	16	16-18	Stamped & Formed	
AT62-16-0144	Female Contact - Socket, Gold-plated	16	16-18	Stamped & Formed	
AT60-16-0122	Male Contact - Pin, Nickel-plated	16	16-18	Stamped & Formed	
AT62-16-0122	Female Contact - Socket, Nickel-plated	16	16-18	Stamped & Formed	
AT60-16-0644	Male Contact - Pin, Gold-plated	16	18-20	Stamped & Formed	
AT62-16-0644	Female Contact - Socket, Gold-plated	16	18-20	Stamped & Formed	
AT60-16-0622	Male Contact - Pin, Nickel-plated	16	18-20	Stamped & Formed	
AT62-16-0622	Female Contact - Socket, Nickel-plated	16	18-20	Stamped & Formed	
AT60-16-0844	Male Contact - Pin, Gold-plated	16	20-22	Stamped & Formed	
AT62-16-0844	Female Contact - Socket, Gold-plated	16	20-22	Stamped & Formed	
AT60-16-0822	Male Contact - Pin, Nickel-plated	16	20-22	Stamped & Formed	
AT62-16-0822	Female Contact - Socket, Nickel-plated	16	20-22	Stamped & Formed	

	Tooling - Stamped & Formed Contacts				
Part	Part Number	Description			
	MFX-3950	Crimp Die - Size 16, 18-20AWG (S&F contacts only)			
	MFX-3953	Crimp Die - Size 16, 16-18AWG (S&F contacts only)			
	MFX-3975	Crimp Die - Size 16, 14-16AWG (S&F contacts only)			
	MFX-3990	Crimp Die - Size 16, 20-22AWG (S&F contacts only)			
	ATT-16-00	Hand Crimp Tool - Size 16, 14-16AWG (S&F contacts only)			
	ATT-16-01	Hand Crimp Tool - Size 16, 18-20AWG (S&F contacts only)			
	ATT-1612-03	Hand Crimp Tool - Size 16, 20-22AWG (S&F contacts only)			

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 09/2021

MagnaMate™ ATHP - DuraMate™ AHDP - DuraMate™ AHDM Series - Contact Size 12 Options

Machined Contacts, Sockets & Pins					
Part Number	Description	Size	AWG	Type	
AT60-204-12141-10	Male Contact - Pin, Nickel-plated	12	10-12	Machined	
AT62-203-12141-10	Female Contact - Socket, Nickel-plated	12	10-12	Machined	
AT60-220-1231	Male Contact - Pin, Gold-plated	12	12-14	Machined	
AT62-210-1231	Female Contact - Socket, Gold-plated	12	12-14	Machined	
AT60-204-12141	Male Contact - Pin, Nickel-plated	12	12-14	Machined	
AT62-203-12141	Female Contact - Socket, Nickel-plated	12	12-14	Machined	

Smaller AWG for	DiagnosticGrade™ Machined Contacts, Sockets & Pins • Smaller AWG for Diagnostic Applications • Gold-plated • Increased Mating Cycles • Cost-effective				
Part Number	Description	Size	AWG	Type	
65-54749	Male Contact - DiagnosticGrade™, Pin, Gold-plated	12	20	Machined	
AT62-210-1231-1820	Female Contact - DiagnosticGrade™, Socket, Gold-plated	12	20	Machined	

	Tooling - Machined Contacts			
Part	Part Number	Description		
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)		
33	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)		

Contact Removal Tools			
Part	Part Number	Description	
	AT11-337-1205	Contact Removal Tool, Plastic, Size 12	
	A114017	Sealing Plug, Size 12, White	

Stamped & Formed Contacts, Sockets & Pins					
Part Number	Description		AWG	Туре	
AT60-12-0244	Male Contact - Pin, Gold-plated	12	10-12	Stamped & Formed	
AT62-12-0244	Female Contact - Socket, Gold-plated	12	10-12	Stamped & Formed	
AT60-12-0222	Male Contact - Pin, Nickel-plated	12	10-12	Stamped & Formed	
AT62-12-0222	Female Contact - Socket, Nickel-plated	12	10-12	Stamped & Formed	
AT60-12-0144	Male Contact - Pin, Gold-plated	12	12-14	Stamped & Formed	
AT62-12-0144	Female Contact - Socket, Gold-plated	12	12-14	Stamped & Formed	
AT60-12-0166	Male Contact - Pin, Nickel-plated	12	12-14	Stamped & Formed	
AT62-12-0166	Female Contact - Socket, Nickel-plated	12	12-14	Stamped & Formed	

Tooling - Stamped & Formed Contacts				
Part	Part Number	Description		
	MFX-3973	Crimp Die - Size 12 (S&F contacts only)		
	MFX-3985	Crimp Die - Size 12 (S&F contacts only) 10-12AWG -02XX Series		
	ATT-12-00	Hand Crimp Tool - Size 12, 12AWG (S&F contacts only)		
	ATT-12-01	Hand Crimp Tool - Size 12, 10AWG (S&F contacts only)		

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 01/2022

ATHD Series™ - Contact Size 8 Options

Machined Contacts, Pins and Sockets					
Part Number	Description Siz		AWG	Туре	Amps
AT60-204-08141	Male Contact - Pin, Copper Alloy, Nickel-Plated	8	8-10	Machined	60A
AT62-203-08141	Female Contact - Socket, Copper Alloy, Nickel-Plated	8	8-10	Machined	60A
AT60-204-08141-16	Male Contact - Pin, Copper Alloy, Nickel-Plated	8	6	Machined	60A
AT62-203-08141-16	Female Contact - Socket, Copper Alloy, Nickel-Plated	8	6	Machined	60A

Tooling - Machined Contacts				
Part	Part Number	Description		
	WA23	Heavy Duty Pneumatic Crimp Tool -Uses Universal Positioner Part No. WA23-101DA and Crimp Locator MFX-3961		
	WA23-2	Die Assembly -for CA-5E12 Heavy Duty Pneumatic Crimp Tool, Size 8		
•	WA23-3	Die Assembly -for CA-5E12 Heavy Duty Pneumatic Crimp Tool, Size 6		
Waging St.	WA23-10	Contact Locator, Size 6 and Size 8		
THE AND	96-978-22	Crimper and Dies -for Size 10mm ² -185mm ² Wires		

Contact Removal Tools				
Part	Part Number	Description		
	AT114008	Contact Removal Tool, Plastic, Size 8, 8-10AWG		