




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/20/09	D.GRIFFIN

2X #4-40 JACKSCREW



WIRE MAP	
DVI-D CONN	TERMINAL BLOCK
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
10	10
11	11
12	12
13	13
14	14
15	15
17	17
18	18
19	19
20	20
21	21
22	22
23	23
24	24
SHELL	GND



**NOTES:**

1. UNIT TO BE TESTED FOR CONTINUITY
2. UNIT TO BE INDIVIDUALLY PACKAGED IN A POLYBAG.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] $\leq 60$ [1524] = +1 [25] / -0 $> 12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $> 60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $> 120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $> 300$ [7620] = +5% / -0%  ALL OTHER DIMENSIONAL TOLERANCES: .XX = .15 .X = .3 .XX = .15	APPROVALS DRAWN BY D. CASTRO CHECKED BY M. SEDLESKI APPROVED BY G. PEPIN	DATE 1/16/09 1/16/09 1/16/09	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845				
	CATEGORY AUDIO/VIDEO			PRODUCT DESCRIPTION DVI-D DUAL LINK F, FIELD TERMINAL			
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR		SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. DVIDDLFT
	SCALE: NONE		CAD FILE: DVIDDLFT.SLDDRW		SHEET 1 OF 1		