





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2013.10.30	劉宗良
02		依業務要求增加電鍍碼	2015.12.15	馮國東
C1		依業務要求新增5PIN和10PIN	2016.01.14	黃超
C2		修正圖面PCB Layout比例錯誤	2016.04.16	黃超

Specifications
 Current Rating:1.0Amp
 Insulation Resistance:1000MΩ Min.
 Dielectric Withstanding Voltage:300VAC
 Contact Resistance:20mΩ Max.
 Operating Temperature:-40°C to +105°C
 Materials
 Contact Material:Phosphor Bronze
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 LCP or the equivalent material
 All materials must meet GREENCONN hazardous substances control standards.

PIN NO.	A	B	C	D	E	F
2*05	5.08	9.50	11.40	8.30	7.30	9.08
2*06	6.35	10.77	12.70	9.57	8.57	10.35
2*10	11.43	15.85	17.80	14.65	13.65	15.43
2*13	15.24	19.66	21.60	18.46	17.46	19.24
2*25	30.48	34.90	36.80	33.70	32.70	34.48

Recommended P.C.Board Layout
 (Tolerance:±0.05)



Pin NO.	Dim.H
≤25pin	0.12
>25pin	0.15

Ordering Information

G BEC202 - XX XX B 001 C 1 A X

No. of Pins per Row
06 13 25

Standard Plating
 79=5u"Au/80~160u"Matte Tin
 77=15u"Gold/Matte Tin
 78=30u"Gold/Matte Tin

Standard Packing
 F= (Finished Product+CAP),Tape&Reel

格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE	
X.*±5.0°	X.±0.30
.X*±3.0°	.X±0.25
.XX*±2.0°	.XX±0.15
.XXX*±1.0°	.XXX±0.10

DESIGNED: 黃超	DATE: 2016.04.16
CHECKED: 林萬輝	DATE: 2016.04.16
CO SIGNED: 劉北平	DATE: 2016.04.16
APPROVED: 李輝	DATE: 2016.04.16

DWG. NO.	GBEC202-CB1CA
PART NO.	GBEC202-XXXXB001C1AX

TITLE.	PITCH 1.27 MALE CONNECTOR
	SMC Q TYPE SMT TYPE
	H6.70mm 180°

REV.	UNIT.	SCALE.	PAGE.
C2	mm	2:1	1/1