




ISS.	AMEND	DATE
1	ISSUED	17/10/17

Panel cut out (front view)

Specification / Technical Data:

Contact Resistance: 30mΩ MAX


Insulation Resistance : 500MΩ min

Dielectric withstanding voltage: 500V AC one minute

Rated Current 0.5A

Rated Voltage 40V

Temperature Range -30°C to 50°C



ITEM	DESCRIPTION	MATERIAL	FINISH
1	FRAME	ZINC DIECAST	BLACK
2	INSERT	ABS	BLACK
3	SCREW	STEEL	NICKEL
4	HDMI	ALLOY	NICKEL

RoHS
COMPLIANT

TOLERANCE
 NO DEC. PLACE ±
 1 DEC. PLACE ±
 2 DEC. PLACE ±
 HOLE Ø ±
 ANGLES ±
 UNLESS
 OTHERWISE STATED

Cliff Electronic Components Ltd.
 76 Holmethorpe Avenue, Holmethorpe Industrial Estate,
 Redhill, Surrey, RH1 2PF, England, UK
 Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

 THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED
 TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2017

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

3rd ANGLE PROJECTION:



DO NOT SCALE

MATERIAL: SEE TABLE

FINISH: SEE TABLE

DRAWN: T.J.O.

APPROVED: D.P.J.

TITLE: XLR HDMI FT - BLACK METAL

DRWG. No. CP30122

FORM: A4DRWGH