






RVPX-JE216EXX		
REV. A	SHEET 1 OF 2	DOCUMENT NO.
REVISIONS		
LTR	DESCRIPTION	DATE
A	INITIAL RELEASE	17-DEC-19



PC BOARD LAYOUT
(CONNECTOR SIDE)
SCALE 4/1

TABLE 1

PLATING THICKNESS AND MATERIAL BY PART NUMBER			
PART NUMBER	GOLD IN CONTACT AREA	COMPLIANT	NICKEL OVERALL
RVPX-JE216EM1	50 μ-INCH MIN	50 μ-INCH MIN TIN	50 μ-INCH MIN
RVPX-JE216EM2	50 μ-INCH MIN	50 μ-INCH MIN TIN-LEAD	50 μ-INCH MIN
RVPX-JE216EC1	30 μ-INCH MIN	50 μ-INCH MIN TIN	50 μ-INCH MIN
RVPX-JE216EC2	30 μ-INCH MIN	50 μ-INCH MIN TIN-LEAD	50 μ-INCH MIN



- 4 ADDITIONAL CONNECTOR-SIDE KEEPOUT AREA REQUIRED IF CONNECTOR-SIDE EXTRACTION TOOL IS TO BE USED.
- 3 SEE TABLE 1 FOR PART NUMBER AND FINISHES
- 2 PTH CALLOUT
TYPICAL HOLE
Ø0.43-.47 DRILL
Ø0.36 ± 0.05 FINISH HOLE
Ø0.75 PAD
- 1 HOUSING: GLASS FILLED LCP, UL94 - V0
CONTACT: Cu ALLOY

THE USE OF THIS DOCUMENT IS UNLIMITED. HOWEVER, DOCUMENTS REFERENCED HEREON MAY CONTAIN LIMITED RIGHTS DATA.	
RELEASED / Jan. 14 2020, 2:39:00 PM	NONE
DOCUMENT NO. RVPX-JE216EXX	SHEET 1 OF 2
REV. A	

PRO/ENGINEER INFORMATION	
Pro/e Model Used:	RVPX-JE216EXX.ASSEM
Drawing Name:	RVPX-JE216EXX

UNLESS OTHERWISE SPECIFIED		SPECIFICATIONS		POS	QTY	PART NUMBER	DESCRIPTION	NOTE
LINEAR DIMENSIONS ARE IN MILLIMETERS TOLERANCES: .XXXX = ±. - ANGLES = ±1° .XXX = ±. - .XX = ±.13 .X = ±.5 DIM. & TOL. PER ASME Y14.5M; DRM PER MIL-DTL-31000; OTHER Amphenol Sds. PER 9-3800 LEGENDS: = FLAG NOTE CALL OUT REFERENCE ONLY		MATERIAL SPEC.		APPROVALS		DATE	PARTS LIST	
		N/A		PREPARED BY S.LANGELIER		17-DEC-19	AMPHENOL CORPORATION 40-60 DELAWARE AVENUE SIDNEY, N.Y. 13838 CONNECTOR ASSEMBLY, BACKPLANE VERTICAL RECEPTACLE, 16 POS, END RVPX EVO 2	
		PROCESS SPEC.		ENGINEER IN CHARGE S.LANGELIER				
		9-3895 9-3856-5		DESIGN MANAGER G. PECK			DESIGN ACTIVITY GROUP BOARD LEVEL	
				THIRD ANGLE PROJECTION			SIZE C	
							CAGE CODE 77820	
							DOCUMENT NO. RVPX-JE216EXX	
							REV. A	
							SCALE: 4/1	
							SHEET 1 OF 2	

REAR TRANSITION MODULE APPLICATION

