



(b) STRIPPING DIMENSIONS

NOTES:

1. MATERIAL: COPPER ALLOY

2. PLATING:

ITEM 1: SEE TABLE

ITEM 2: GOLD FLASH over NICKEL

ITEM 3: NICKEL PLATED

3. CRIMPING: USE CRIMP TOOL 360X10409X

WITH TOOL INSERT 360X20029X

SELECTOR SETTINGS: 7 FOR AWG 8

6 FOR AWG 10

(c) 4. CURRENT RATING: PER UL 1977 / CSA - C22.2 No.182.3 (E228329)
-40A

-50A only when used with cable AWG 8 and in combination with

2W2C connectors per following part number system:

Cat. No. 302W2, 302W2 followed by C, followed by P or S,

followed by XX, followed by 99, followed by A1 through A8, C1 through C6,

D1 through D6, E1 through E6, F1 through F6, G1 through G4,

H1 through H4, K1 through K4, L1 through L4, N1 through N4 or

P1 through P4, W1, W2 or S9, followed by 0X or 0A to 0W

when used in conjunction with the following contacts and

pins 131A, 132A, 131C, 132C, 131J and 132J followed by 11049X

PLATING ITEM 1	PART-NO.
GOLD FLASH over NICKEL	132A11049X
min. 30µin HARD GOLD over min. 50µin NICKEL	132C11049X
min. 50µin HARD GOLD over min. 50µin NICKEL	132J11049X

(b)

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND	finish			tolerance		dim. in mm	scale:			
	SEE NOTES			ISO 2768-m			5:1			
				date		name		material:		
				23.03.98		Barcinski		SEE NOTES		
			appd.		23.03.98		Mickenbecker			
			norm				title:			
2 x c			Ä4283	17.04.12	K.H.	d-old	HIGH POWER CONTACT FEMALE			
4 x b			Ä3854	19.01.11	K.H.		CRIMP VERSION AWG 8-10 (c)			
a			Origin				D-SUB COMBINATION			
rev.			description		date		name		dwg no:	
									13K11F0A	
									DIN-A3	
									sh: 1	
									part no: SEE TABLE	

