


SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN mm)

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)



NOTE: 1 DA MISURARSI CON LA MOLLA IN POSIZIONE ORIZZONTALE
(Measured when spring is horizontal)
2 ADATTO PER TERMINALE MASCHIO CON FORO, SECONDO TABELLA FIAT
91319 FOGLIO 2 (TIPO A) (Suitable for Tab 0.8 THK with hole)
3 MASSIMA SCIABOLATURA AMMESSA: 18 mm PER METRO (Camber: 18mm/m)
4 SENSO DI USCITA DEL TERMINALE DALLA BOBINA. (P.N. -2)
(Direction off top of reel)

REV.	REVISIONI (REVISION RECORD)	DIS. DATA (DATE)	19 JUL 16	3-XII 87	APP. DATA (DATE)
A2	ECR-16-009345	L.P.			
A	In Produzione	ES			

STAGNATO (Tin Plated)	(Brass) OTTONE OT 70	281828-2
---	(Brass) OTTONE OT 70	281828-1
FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)
CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO
THIS DRAWING IS UNPUBLISHED		RELEASE FOR PUBLICATION
© COPYRIGHT 1986 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING		
TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)	DIA. ISOLANTE (INS. DIA. RANGE)	RANGO FILO (WIRE RANGE)
	3.6-4.3 mm	2.5-4.0 mm ²
ANGOLI CANGLED	±0.3	
DIS. COR. 2	± 2°	
DESCRIZIONE (DESCRIPTION)		(MARK I)
POSITIVE LOCK REC.		
LOC. SIZE NUMERO (CNS NO)	REV.	FOGLIO (SHEET)
I A3C-281828	A2	01