





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/25/12	D.GRIFFIN
B	ECN 7563: ADDED HDMI WITH HIGH SPEED WIRE MAP, UPDATE ROHS AND FORMAT	8/22/14	D. CASTRO




HDMI WIRE MAP (HIGH SPEED WITH ETHERNET)



FIELD TERM WIRE MAP	
HDMI 19 PIN	TERMINAL BLOCK
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
10	10
11	11
12	12
13	13
14	14
15	15
16	16
17	17
18	18
19	19
GROUND	GND

CONNECTOR, HDMI 19 PIN RECEPTACLE FLANGE MOUNT (GOLD PLATED CONTACTS)



NOTES:

- ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.

REGULATORY COMPLIANCE:

CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\le 12 [305] = +1 [25] / -0$ $> 12 [305] \le 60 [1524] = +2 [51] / -0$ $> 60 [1524] \le 120 [3048] = +4 [102] / -0$ $> 120 [3048] \le 300 [7620] = +6 [152] / -0$ $> 300 [7620] = +5\% / -0\%$	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. CASTRO	10/25/12		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY D. PARHAM	10/25/12	PRODUCT DESCRIPTION	
PROJECTION	APPROVED BY P. MCNEIL	10/25/12	HDMI F CONN, FIELD TERMINATION	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. HDFT	REV. B
			SCALE: NONE	CAD FILE: HDFT.SLDDRW
				SHEET 1 OF 1