

NOTES:



1. RESISTANCE @ 25°C : 50KΩ ± 1%
2. BETA VALUE (0/50°C) : 4035K ± 1%
3. OPERATING TEMPERATURE RANGE : -40°C TO +250°C.
4. THERMAL TIME CONSTANT : 15SEC IN WATER
5. VOLTAGE BREAKDOWN STRENGTH : 1500V AC FOR 3SEC.
6. INSULATION RESISTANCE : A MINIMUM OF 100MΩ @ 500VOLTS DC.
7. DISSIPATION FACTOR : 1mW/°C.
8. LASER MARKING "MOLEX-DATE CODE(MM/YY)" & "XXK(R25-value) XXXX(B-value)"

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:				molex					
	DIMENSION UNITS	SCALE										
▽/A = 0	mm	NTS	EC NO: 727818 DRWN: NANDAK 2022/11/09 CHK'D: RBBHASKAR 2022/11/15 APPR: RBBHASKAR 2022/11/15 INITIAL REVISION: DRWN: RAVIKM 2022/01/30 APPR: RBBHASKAR 2022/02/18				GLASS NTC PROBE A -50K±1%,B4035,L300					
▽/E = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)						PRODUCT CUSTOMER DRAWING					
▽/Z = 0	ANGULAR TOL ± °						DOCUMENT NUMBER			DOC TYPE	DOC PART	REVISION
DIVISIONAL SYMBOLS	4 PLACES	±					2185373909			PSD	000	A2
	3 PLACES	±	MATERIAL NUMBER			CUSTOMER						
	2 PLACES	±	2185373909			GENERAL MARKET						
	1 PLACE	±	SERIES			SHEET NUMBER						
	0 PLACES	±	A3-SIZE 218537			1 OF 2						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIRD ANGLE PROJECTION		DRAWING		SERIES					
					A3-SIZE		218537					

RESISTANCE VS TEMPERATURE CHARACTERISTICS

TEMP(°C)	Rmin(KΩ)	Rnom(KΩ)	Rmax(KΩ)
-40	1689.446	1768.460	1850.985
-35	1206.272	1258.400	1312.649
-30	887.056	922.520	959.306
-25	664.871	689.441	714.849
-20	497.166	514.028	531.408
-15	374.123	385.702	397.600
-10	281.815	289.707	297.790
-5	214.745	220.154	225.676
0	164.268	167.950	171.697
5	126.975	129.484	132.029
10	98.953	100.654	102.374
15	77.932	79.081	80.239
20	61.896	62.663	63.432
25	49.500	50.000	50.500
30	39.644	40.133	40.623
35	31.919	32.382	32.848
40	25.824	26.254	26.688
45	20.991	21.384	21.782
50	16.731	17.082	17.439
55	14.063	14.383	14.709
60	11.593	11.880	12.172
65	9.605	9.861	10.123
70	8.000	8.228	8.462
75	6.700	6.903	7.112
80	5.643	5.824	6.010
85	4.782	4.943	5.109
90	4.088	4.232	4.382
95	3.509	3.638	3.772
100	3.022	3.138	3.258
105	2.609	2.713	2.821
110	2.258	2.351	2.448
115	1.957	2.041	2.129
120	1.699	1.775	1.853
125	1.478	1.545	1.616
130	1.287	1.347	1.411
135	1.122	1.177	1.234
140	0.980	1.029	1.081
145	0.858	0.902	0.948
150	0.752	0.792	0.834

TEMP(°C)	Rmin(KΩ)	Rnom(KΩ)	Rnom(KΩ)
155	0.6592	0.695	0.7325
160	0.5856	0.618	0.6523
165	0.5222	0.552	0.583
170	0.4671	0.494	0.5226
175	0.4189	0.444	0.4697
180	0.3765	0.399	0.423
185	0.3391	0.36	0.3818
190	0.3059	0.325	0.3452
195	0.2765	0.294	0.3126
200	0.2503	0.266	0.2835
205	0.227	0.242	0.2576
210	0.2061	0.22	0.2344
215	0.1875	0.2	0.2136
220	0.1707	0.182	0.1949
225	0.1558	0.167	0.1781
230	0.1425	0.153	0.1632
235	0.1306	0.14	0.1499
240	0.1198	0.129	0.1378
245	0.1103	0.118	0.127
250	0.1018	0.109	0.1174

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:				
	$\nabla_A = 0$ $\nabla_E = 0$ $\nabla_V = 0$	DIMENSION UNITS: mm SCALE: NTS					
DIVISIONAL SYMBOLS	4 PLACES ±	EC NO: 727818	DRWN: NANDAK	2022/11/09	PRODUCT CUSTOMER DRAWING		
	3 PLACES ±	CHK'D: RBBHASKAR	APPR: RBBHASKAR	2022/11/15			
	2 PLACES ±	INITIAL REVISION:		DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
	1 PLACE ±	DRWN: RAVIKM	2022/01/30	2185373909	PSD	000	A2
0 PLACES ±	APPR: RBBHASKAR	2022/02/18					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
			A3-SIZE	218537	2185373909	GENERAL MARKET	2 OF 2