



M8 FEMALE
VIEWS FROM THE FRONT SIDE

3 POLE




Pin	Wire color
1	BROWN
3	BLUE
4	BLACK

4 POLE



Pin	Wire color
1	BROWN
2	WHITE
3	BLUE
4	BLACK

5 POLE



Pin	Wire color
1	BROWN
2	WHITE
3	BLUE
4	BLACK
5	GREY

PART NO. MATRIX

40 = M8x1
SINGLE ENDED

POLES:
3 = 3 POLES
4 = 4 POLES
5 = 5 POLES

HEADER:
001 = FEMALE 90°

CABLE:
B41 = 0,25mm²,
TPU BK
B36 = 0,34mm²,
TPU OG


UNIT:
M = METER

LENGTH EXAMPLE:
010 = 1 m
050 = 5 m
100 = 10 m

COUPLING NUT:
BLANK = KNU
7 = TEFLON KNU
OVERMOULD:
BLANK = BK
A = GY
Y = YE
R = RD
H = 2x I/D CARIERR
AND ALWAYS WITH
THE CABLE B3

OPTIONS

FEMALE RIGHT ANGLED PLUG(M8 PLUG)



BOM

8	(SEE MATRIX)	ID-CARRIER	PVC	TRANSPARENT
7	1	WRAP LABEL STANDARD	VINYL	YELLOW
6	1	GASKET	FKM	RED
5	1	INSERT M8 FE XP	PUR	BLACK
4	3/4/5	CONTACT FE	COPPER	SELECTED GOLD OVER NICKEL
3	1	M8 COUPLING NUT	SEE PART LIST	SEE PART LIST
2	-	MOULDING MATERIAL	TPU	SEE PART LIST
1	-	CABLE	TPU	SEE PART LIST
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH / COLOR

TECHNICAL DATA :	
TEMPERATURE RANGE	-25°C TO +80°C
CONTACT CURRENT RATING	3A
VOLTAGE RATING	3 POLES 60V
	4-5 POLES 30V
PROTECTION CLASS	IP 67

FUNCTIONAL SYMBOLS
FA= 0
FE= 0
FE= 0

DIVISIONAL SYMBOLS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE
2:1

GENERAL TOLERANCES (UNLESS SPECIFIED)
ANGULAR TOL ± 1.0 °

4 PLACES ±
3 PLACES ±
2 PLACES ±
1 PLACE ±
0 PLACES ±

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 684766
DRWN: SSM
CHK'D: RSILLER
APPR: RSILLER

2021/11/03
2021/11/10
2021/11/10

INITIAL REVISION:
DRWN: WSTRASZKIEWI
APPR: MIWASIECZKO

2014/09/02
2014/09/08

THIRD ANGLE PROJECTION

DRAWING
A3-SIZE

SERIES
120086

MATERIAL NUMBER
SEE PART LIST

CUSTOMER
GENERAL MARKET

SHEET NUMBER
1 OF 2

molex

CSE M8 XP AC FE RA
TPU XM

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER
SD-120086-010

DOC TYPE
PSD

DOC PART
001

REVISION
B4

