
** Not all features are shown in this drawing. For more detailed information, please contact your Fair-Rite representative.

UNCONTROLLED ~CATALOG~ DRAWING

SIZE	PART NO.	REV.
В	2944666671	\sim



ELECTRICAL SPECIFICATIONS

IMPEDANCE (OHMS)				
10 MHz	50 MHz	100 MHz		
300 Min.	750 Min.	820 Min.		

LEAD LENGTHS TRIMMED TO 1/2" FROM CORE TESTED WITH 2-1/2 TURNS #24 AWG

DIMENSIONS

BOLD NUMBERS ARE IN MILLIMETERS

LIGHT NUMBERS ARE IN INCHES

NOTES:

- 1 CHIPS, CRACKS, AND APPREARANCE TO MEET FAIR-RITE VISUAL INSPECTION CRITERIA FOR GENERIC MULTI-HOLE WOUND BEADS.
- 2 IMPEDANCE MEASURED ON AN E4991A USING A 16092A TEST FIXTURE.
- 3 WIRE MEETS SOLDERABILITY SPECIFICATION WHEN TESTED PER SOP# ELC-57.
- 4 PART MEETS FAIR-RITE PRODUCTS CORP. SOP# ELC-55, FOR THERMAL SHOCK RESISTANCE.
- 5 WIRE LOOPS SHOULD BE UNIFORM IN LENGTH.
- 6 PACKAGING: THIS PART IS BULK PACKED.

TITLE WOUND BEAD

DRAWN BY DATE D. FOOTE 9/30/2019 B 294466671 ~

APPRVD BY SCALE: NONE SHEET 1 OF 1

FR# 44