




- NOTES 1 THIS PRODUCT IS APPLY TO THE WIRE AWG#30(WIRE JACKET DIAMETER ϕ 0.71 MAX).
2 PER PACK : 100 CONTACTS.
3 RECOMMEND CABLE PREPARATION DIMENTION ARE SHOWN IN FIG.1.
4 APPLICABLE OPERATION CRIMP TOOL:HR25-TA3032HC

				1	PHOSPHER BRONZE		CONTACT AREA: GOLD 0.2μm min. TERMINAT AREA:NICKEL PLATING 1μm min. UNDER PLATING: NICKEL PLATING 1μm min.					
NO.	MATERIAL		FINISH . REMARKS			NO.	MATERIAL		FINISH . REMARKS			
UNITS mm			SCALE 10 : 1		COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED		DATE
 HIROSE ELECTRIC CO., LTD.				APPROVED :EJ. KUNII		15.10.05		DRAWING NO.		EDC-110400-00-00		
				CHECKED :EJ. KUNII		15.10.05		PART NO.		HR25-PC-111		
				DESIGNED :WR. AJIRO		15.10.05		CODE NO.		CL125-0419-1-00		
				DRAWN :WR. AJIRO		15.10.05				 1 1		