


Oct.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case that the application demands a high level of reliability, such as automotive,  
please contact a company representative for further information.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
2	DIS-C-000490	T.H	E.K	07.01.31					



- NOTES
- 1 TOTAL LENGTH BECOMES 28.8±1 WHEN 6 IS SCREWED INTO 1 COMPLETERY.
  - 2 THE RECOMMENDED CLUMP TORQUE OF REF. NO.6 TO BE 0.5N · m.  
LOCTITE 271, LOCPRIMER 7649,HENKEL JAPAN IS RECOMMENDED TO PREVENT REF. NO.6 FROM LOOSENING.  
SPACER FOR ASSEMBLY IS AVAILABLE HR30-6P-T02.
  - 3 TABLE FOR ASSEMBLY AND SOLDERING IS AVAILABLE HR30-6R-6P-T01.
  - 4 SURFACE PLATING: GOLD PLATING 0.2μ m min.  
UNDER PLATING: NICKEL PLATING 2μ m min.
  - 5 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER,  
DEPENDING ON THE CABLE STRUCTURE.  
PLEASE CONFIRM BEFORE THE USE.

3	PPS	(BLACK)	UL94V-0	6	PBT	(BLACK)	UL94V-0
2	BRASS	4		5	CR	(BLACK)	
1	PPS	(BLACK)	UL94V-0	4	POLYACETAL	(NATURAL)	
NO.	MATERIAL	FINISH	REMARKS	NO.	MATERIAL	FINISH	REMARKS
CODE NO. (OLD)			DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
			M.HANYU	H.NAGANO	E.KUNII	M.SATO	
			'05. 8 . 8	'05. 8 . 8	'05. 8 . 10	'05. 8 . 10	
DRAWING NO.			PART NO.				
EDC3-112570-71			HR30-6JA-6P(71)				
SCALE			CODE NO.				
5 : 1			CL130-2018-7-71				1/1
UNITS							
mm							

TO  
R