


Oct.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case that the application demands a high level of reliability, such as automotive,
 please contact a company representative for further information.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
2	DIS-C-000490	T.H.E.K		07.01.31					



- NOTES
- ① TOTAL LENGTH BECOMES 29.8±1 WHEN ⑧ IS SCREWED INTO ① COMPLETELY.
 - ② TABLE FOR ASSEMBLY AND SOLDERING IS AVAILABLE HR30-6P-6S-T01.
 - ③ THE RECOMMENDED CLAMP TORQUE OF REF. NO.⑧ TO BE 0.5N·m.
 LOCTITE 271, LOCPRIMER 7649, HENKEL JAPAN IS RECOMMENDED TO PREVENT REF. NO.⑧ FROM LOOSENING.
 SPACER FOR ASSEMBLY IS AVAILABLE HR30-6P-T02.
 - ④ SURFACE PLATING: GOLD PLATING 0.2μm min.
 UNDER PLATING: NICKEL PLATING 2μm min.
 - ⑤ THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER,
 DEPENDING ON THE CABLE STRUCTURE.
 PLEASE CONFIRM BEFORE THE USE.

MATING MARK
 (PRINTED IN WHITE)

4	PBT	(BLACK)	UL94V-0	8	PBT	(BLACK)	UL94V-0
3	SIR	(RED)		7	POLYACETAL	(NATURAL)	
2	BRONZE ALLOY	④		6	CR	(BLACK)	
1	PPS	(BLACK)	UL94V-0	5	STAINLESS STEEL		
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS	

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	M.HANYU	H.NAGANO	E.KUNII	M.SATO	
	'05. 8. 8	'05. 8. 8	'05. 8. 10	'05. 8. 10	

	DRAWING NO. EDC3-112512-71	PART NO. HR30-6PA-6S(71)
SCALE 5 : 1 UNITS mm	HIROSE ELECTRIC CO., LTD	CODE NO. CL130-0019-9-71

TO
R