



- NOTES
- ① PLATING(REF.NO.③.④)  
 CONTACT AREA : GOLD 0.2μm min  
 OTHERS : GOLD AND NICKEL  
 UNDER PLATING : NICKEL 2μm min
  - ② THE RECOMMENDED CLAMP TORQUE OF REF.NO.⑧ TO BE 1.5 TO 2N·m.  
 THREAD LOCKER TO THE THREADED PORTION OF REF.NO.① IS RECOMMENDED TO PREVENT REF.NO.⑧ FROM LOOSING.  
 RECOMMENDED THREAD LOCKER:LOCTITE 271, HENKEL JAPAN LTD.
  - ③ WHEN THIS CONNECTOR IS MOUNTED ON TO PANEL, BE CAREFUL REF.NO.⑥ IS ASSEMBLED SURELY INTO THE GROOVE OF REF.NO.⑥ AS SHOWN IN THIS FIGURE TO KEEP WATERPROOF EFFECTIVENESS.

4	COPPER ALLOY	①	8	BRASS	NICKEL PLATING
3	COPPER ALLOY	①	7	PHOSPHOR BRONZE	NICKEL PLATING
2	PPS	(BLACK) UL94V-0	6	CHLOROPRENE RUBBER	(BLACK)
1	ZINC ALLOY	NICKEL PLATING	5	PHOSPHOR BRONZE	NICKEL PLATING
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS	mm	SCALE	4 : 1	COUNT	1
		DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
		DIS-C-002180	HK. NAMAI	HY. KISHI	11. 05. 13
APPROVED : MR. YOSHIDA		05. 01. 05	DRAWING NO. EDC3-114246-00		
CHECKED : MO. SATOH		05. 01. 05	PART NO. LF10WBR-12P		
DESIGNED : YH. YAMADA		05. 01. 05	CODE NO. CL136-1007-3-00		
DRAWN : YH. YAMADA		05. 01. 05	② 1/1		