



- NOTES
- 1 ONE EXAMPLE OF THE ROTATION OF REF. NO. ⑨ TO REF. NO. ① IS SHOWN.
 - ② THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑨: 3N·m.
 LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. ⑨ FOR LOOSENING.
 - 3 THIS PRODUCTS TO BE USED WITH CABLE CLAMP, JR13WCC-*(72).
 * DESIGNATE DIAMETER(mm) OF APPLICABLE CABLE.
 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE, PLEASE BEFORE THE USE.

NO.	MATERIAL	FINISH	REMARKS	NO.	MATERIAL	FINISH	REMARKS
5	POLYACETAL	(WHITE)					
4	DIALLYL PHTHALATE	(BLACK)	UL94V-0	9	ZINC ALLOY	CHROME PLATING	
3	DIALLYL PHTHALATE	(BLACK)	UL94V-0	8	SILICONE RUBBER	(BLACK)	
2	BRASS	SILVER PLATING 2µm min.		7	BRASS	CHROME PLATING	
1	ZINC ALLOY	CHROME PLATING		6	SILICONE RUBBER	(RED)	

UNITS	SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	△				
APPROVED : SU. OBARA			13. 04. 11	DRAWING NO. EDC3-111068-71		
CHECKED : SU. OBARA			13. 04. 11	PART NO. RM15WTPZ-4P(71)		
DESIGNED : HY. KISHI			13. 04. 11	CODE NO. CL109-1617-1-71		
DRAWN : HY. KISHI			13. 04. 11	△ 1/1		