PART NUMBER

134-1001-401

REV	ECO	DATE
1	INITIAL RELEASE	08/12/2021

1. MATERIAL AND FINISH:


- 1.1 BODY: BRASS, NICKEL PLATE
- 1.2 CONTACT: BERYLLIUM COPPER, GOLD PLATE
- 1.3 INSULATOR: PTFE
- 1.4 O-RINGS: SILICONE RUBBER

2. ELECTRICAL SPECIFICATIONS:


- 2.1 IMPEDANCE: 50 OHMS NOMINAL
- 2.2 FREQUENCY RANGE: DC-6 GHZ
- 2.3 DIELECTRIC WITHSTANDING VOLTAGE: 1,000 VRMS
- 2.4 INSULATION RESISTANCE: 1,000 MEGOHMS
- 2.5 TEMPERATURE RATING: -65°C TO +165°C

3. MECHANICAL SPECIFICATIONS:

- 3.1 CONNECTOR DURABILITY: SMA 250 CYCLES MIN. MCX 500 CYCLES MIN.
- 3.2 PANEL THICKNESS: .312 [8.0] MAX.
- 3.3 CONNECTOR MEETS: CECC 22 220, MIL-PRF-39012, MIL-STD-348



[20.24] .797



cinch CONNECTIVITY SOLUTIONS	Model No: 134-1001-401/410		JOHNSON
This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable,	ROHS M (EU)/2015/863 COMPLIANT	3RD ANGLE PROJECTION	SMA JACK TO MCX JACK BULKHEAD ADAPTER WITH HEX NUT
and issued with the clear understanding that it is not traced or copied without permission and is returnable upon demand.	800.±XXX.	Drawn by: TOMMY REN	Drawing No. REV. 134-1001-401/410
INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2009.	.XXXX±.004 ANGLES±5°	Date: 08/12/2021	Size DO NOT SCALE Workmanship Std: Sheet NONE 1 OF 1