




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION MAY, 1995.  
 © COPYRIGHT 1995 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
J		B	REVISED	11JUN07	Y.S Y.N
		C	REVISED PER ECO-17-002393	25MAY17	B.J S.Y

AS SHOWN: TYPE-1




D-D (SCALE 2:1)

⚠ TRAY TYPE-1 AND TYPE-2 MUST BE  
 PILED UP BY TURNS.  
 (REFER TO PACKING SPECIFICATIONS)



E (SCALE 2:1)



DETAIL C (SCALE 4:1)

**OBSOLETE**

5	50	43	21.7	50	2013011-3
ROW	QTY	B	A	POS.	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Y.SHINO 8MAY07	Tyco Electronics AMP K.K. Kawasaki, Japan		
DIMENSIONS: MM		CHK Y.NAKAZAWA 8MAY07	NAME		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T.FUTATSUGI 8MAY07	PRODUCT SPEC		
0 PLC ± 0.3		108-60047			
1 PLC ± 0.3		APPLICATION SPEC			
2 PLC ± 0.3		114-5255			
3 PLC ± 0.3		SIZE CAGE CODE DRAWING NO RESTRICTED TO			
4 PLC ± 0.3		A3 00779 C-2013011			
ANGLES ± 3'		CUSTOMER DRAWING			
FINISH		SCALE 1:2 SHEET 1 OF 2 REV C			

4


3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION MAY, 1995.  
 © COPYRIGHT 1995 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
J		P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-



OBSOLETE

RECOMMENDED P.C. BOARD LAYOUT

△ MATERIAL ; HOUSING : HIGH TEMP THERMO PLASTIC  
UL94V-0  
CONTACT : COPPER ALLOY  
SOLDER PEG : COPPER ALLOY

△ FINISH ; CONTACT  
UNDER PL Ni 0.0013mm MIN ALL OVER.  
CONTACT AREA : 0.00076 MIN Au PL.  
SOLDERING AREA : 0.00005 MIN Au PL.

SOLDER PEG  
UNDER PL Ni 0.0005mm MIN ALL OVER.  
ALL OVER : 0.003mm MIN Sn-Pb PL.

4. SEE PACKING ASSY DWG AS FINAL ASSY PART NUMBER.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		Tyco Electronics		Tyco Electronics AMP K.K.													
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		Kawasaki, Japan													
<table border="1"> <tr><td>0 PLC</td><td>± 0.3</td></tr> <tr><td>1 PLC</td><td>± 0.3</td></tr> <tr><td>2 PLC</td><td>± 0.3</td></tr> <tr><td>3 PLC</td><td>± 0.3</td></tr> <tr><td>4 PLC</td><td>± 0.3</td></tr> <tr><td>ANGLES</td><td>± 3'</td></tr> </table>		0 PLC	± 0.3	1 PLC	± 0.3	2 PLC	± 0.3	3 PLC	± 0.3	4 PLC	± 0.3	ANGLES	± 3'	FINISH		SOFT TRAY ASSY		FH 0.6BTB CONNECTOR	
0 PLC	± 0.3																		
1 PLC	± 0.3																		
2 PLC	± 0.3																		
3 PLC	± 0.3																		
4 PLC	± 0.3																		
ANGLES	± 3'																		
MATERIAL		APVD		PLUG 4H STD Au PLATED 0.00076MM		RESTRICTED TO													
△		△		SIZE		CAGE CODE													
		PRODUCT SPEC		DRAWING NO		A3 00779 C-2013011													
		APPLICATION SPEC		SCALE		SHEET													
		WEIGHT		4:1		2 OF 2													
		CUSTOMER DRAWING		REV		C													

18.8	17.6	21.7	17	14.4	50
E	D	C	B	A	POS