


DO NOT SCALE DRAWING

REVISIONS

ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	DRAWN	08-08-2013	



Part No.	A
TRSRLCBS-6-01	9.5
TRSRLCBS-7-01	11.1
TRSRLCBS-8-01	12.7
TRSRLCBS-10-01	15.9
TRSRLCBS-12-01	19.1
TRSRLCBS-14-01	22.2
TRSRLCBS-16-01	25.4

Bottom Hole: Snap Rivet:Ø4.1-4.2mm;	
Use TR Snap Rivet	Panel Thickness
TRSR-4040	0.1-0.7
TRSR-4050	0.7-1.6
TRSR-4055	1.2-2.2
TRSR-4060	1.5-2.7
TRSR-4070	2.7-3.7
TRSR-4080	3.7-4.7
TRSR-4090	4.7-5.7
TRSR-4100	5.7-6.7
TRSR-4120	7.2-8.7
TRSR-4155	10.7-12.2

- Notes:
- 1.RoHS Compliant;
 - 2.Top Hole:Ø4.0±0.08mm, Panel Thickness:1.57mm;



DESIGN RIGHT. TR FASTENINGS LTD. 2003
UNDER NO CIRCUMSTANCES MUST THIS
DRAWING BE COPIED OR DISCLOSED.
WITHOUT FIRST OBTAINING WRITTEN
AUTHORITY.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETERS.
SURFACE FINISH:
TOLERANCES:
L≤4 = ±0.1 4<L≤15 = ±0.2
15<L≤50 = ±0.3 50<L≤100 = ±0.4

NAME	DATE
DRAWN MARTIN ELLIOTT	08/08/2013
CHK'D	
APP'D	

CUSTOMER PART NO.

MATERIAL
PA66 UL94 V2

HEAT TREATMENT
N/A

FINISH
NATURAL

TITLE
SNAP RIVET LOCKING CIRCUIT
BOARD SUPPORT

DWG NO.
TRSRLCBS-XX-01

A3