



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		D	ECR-14-019277	30DEC2014	RZ	MY

NOTES:

- 1 SINGLE PACKING: ONE CONNECTOR PER LABELED BAG PACKAGED. LABELED PER TEC-107-115
- 2 TRAY PACKAGED
- 3 Ag PLATING
- 4 WHITE BRONZE PLATING
- 5 ELECTRICAL CHARACTERISTICS
FREQUENCY RANGE: DC - 2 GHz
NOMINAL IMPEDANCE: 50 & 75 Ohm
INSULATION RESISTANCE: 5000 MOhm
WORKING VOLTAGE: 500 Volts RMS at Sea Level
DIELECTRIC WITHSTAND VOLTAGE: 1000 Volts RMS Max
CONTACT RESISTANCE:
 CENTER CONTACT: 1.50 mOhm Max
 OUTER CONTACT: 1.00 mOhm Max
VSWR @ 2GHz: 1.35 Max
- 6 MECHANICAL CHARATERISTICS
DURABILITY: 500 Cycles Min
- 7 ENVIRONMENTAL CHARACTERISTICS
OPERATING TEMPERATURE: -40 to +85 DegC



1-1337446-0 / 3-1337446-0 / 6-1337446-0 50ohm




1-1337446-1 / 3-1337446-1 / 6-1337446-1 75ohm

1	1	1	-	-	-	PTFE	INSULATION	5
1	1	1	-	-	-	PTFE	INSULATION	4
1	1	1	1	1	1	PHOSPHOR BRONZE 3	CONTACT	3
-	-	-	1	1	1	PTFE	INSULATION	2
1	-	-	1	-	-	BRASS 4	BODY	1
-	1	1	-	1	1	BRASS 4	BODY	1
3--1	6--1	1--1	3--0	6--0	1--0	MATERIAL	DESCRIPTION	ITEM
3	6	1	3	6	1			
QUANTITY PER ASSY							PARTS LIST	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± 0.5
1 PLC	± 0.3
2 PLC	± 0.2
3 PLC	± -
4 PLC	± -
ANGLES	± -

FINISH

-

DWN	J.SANDWELL	26NOV05
CHK	S.PARLOW	26NOV05
APVD	F.WHEELER-KING	26NOV05
PRODUCT SPEC	-	-
APPLICATION SPEC	-	-
WEIGHT	-	-

CUSTOMER DRAWING



TE Connectivity

BNC PANEL SOCKET 50 OHM & 75 OHM

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1337446	-

SCALE	NTS	SHEET	1 OF 1	REV	D
-------	-----	-------	--------	-----	---