





| P | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|---|-----|---------------------------|-----------|-----|------|
|   | A   | REVISED PER ECN-23-195185 | 23JAN2023 | SS  | RE   |
|   |     |                           |           |     |      |
|   |     |                           |           |     |      |
|   |     |                           |           |     |      |

- 1.WIRE RANGE: 16-14AWG
- 2.INSULATION RANGE: 3.0-4.3 mm
- 3.CONTINUOUS STRIP ON REEL
- 4.PRELIMINARY- NOT RELEASED FOR PRODUCTION



SECTION A-A



SECTION B-B

PRE-TIN BRASS 0.30 THICKNESS

2390259-1

MATERIAL

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN DAISY LI 25MAR2022

CHK ERIC WANG 25MAR2022

APVD ERIC WANG 25MAR2022

PRODUCT SPEC

108-106654

APPLICATION SPEC

114-106546

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME 187 SERIES POSITIVE LOCK

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-2390259

RESTRICTED TO


-

SCALE 3:1

SHEET 1 OF 1

REV A

DIMENSIONS:  
mm



TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC ±  
1 PLC ±0.30  
2 PLC ±0.25  
3 PLC ±0.25  
4 PLC ±  
ANGLES ±

MATERIAL

BRASS

FINISH

-

PRE-TIN PLATED