


DO NOT SCALE DRAWING

REVISIONS

ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	DRAWN	08-08-2013	

Part No.	A
TRLCBSM-2-01	3.2
TRLCBSM-3-01	4.8
TRLCBSM-4-01	6.4
TRLCBSM-5-01	7.9
TRLCBSM-6-01	9.5
TRLCBSM-7-01	11.1
TRLCBSM-8-01	12.7
TRLCBSM-9-01	14.3
TRLCBSM-10-01	15.9



Notes:

- Also available in flame retardant nylon(PA66 UL94V-0);
- Top Hole: Ø3.18±0.05mm, Panel Thickness: 0.79-1.98mm;
- Bottom Hole: Ø3.18±0.05mm, Panel Thickness: 1.57mm.



DESIGN RIGHT. TR FASTENINGS LTD. 2003
UNDER NO CIRCUMSTANCES MUST THIS
DRAWING BE COPIED OR DISCLOSED.
WITHOUT FIRST OBTAINING WRITTEN
AUTHORITY.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETERS.
SURFACE FINISH:
TOLERANCES:
L≤4 = ±0.1 4<L≤15 = ±0.2
15<L≤50 = ±0.3 50<L≤100 = ±0.4

NAME	DATE
DRAWN MARTIN ELLIOTT	08/08/2013
CHK'D	
APP'D	

CUSTOMER PART NO.

MATERIAL

PA66 UL94 V2

HEAT TREATMENT

N/A

FINISH

NATURAL

TITLE

LOCKING PCB SUPPORT

DWG NO.

TRLCBSM-XX-01

A3

PROJECTION



SHEET 1 OF 1