


DO NOT SCALE DRAWING

| REVISIONS |      |             |            |          |
|-----------|------|-------------|------------|----------|
| ZONE      | REV. | DESCRIPTION | DATE       | APPROVED |
|           | A    | DRAWN       | 08-08-2013 |          |

| Part No.          | A    |
|-------------------|------|
| TRMDLSP1-02M-01   | 2.0  |
| TRMDLSP1-03M-01   | 3.0  |
| TRMDLSP1-04M-01   | 4.0  |
| TRMDLSP1-05M-01   | 5.0  |
| TRMDLSP1-06M-01   | 6.0  |
| TRMDLSP1-07M-01   | 7.0  |
| TRMDLSP1-08M-01   | 8.0  |
| TRMDLSP1-09M-01   | 9.0  |
| TRMDLSP1-10M-01   | 10.0 |
| TRMDLSP1-12M-01   | 12.0 |
| TRMDLSP1-14M-01   | 14.0 |
| TRMDLSP1-16M-01   | 16.0 |
| TRMDLSP1-18M-01   | 18.0 |
| TRMDLSP1-20M-01   | 20.0 |
| TRMDLSP1-22M-01   | 22.0 |
| TRMDLSP1-26.5M-01 | 26.5 |
| TRMDLSP1-35M-01   | 35.0 |



Notes:

- Also available in flame retardant nylon(PA66 UL94V-0);
- Top Hole:  $\text{Ø}2.5 \pm 0.05\text{mm}$ , Panel Thickness: 1.57mm;
- Bottom Hole:  $\text{Ø}2.5 \pm 0.05\text{mm}$ , Panel Thickness: 1.57mm.



DESIGN RIGHT. TR FASTENINGS LTD. 2003  
 UNDER NO CIRCUMSTANCES MUST THIS  
 DRAWING BE COPIED OR DISCLOSED.  
 WITHOUT FIRST OBTAINING WRITTEN  
 AUTHORITY.

UNLESS OTHERWISE SPECIFIED:  
 DIMENSIONS ARE IN MILLIMETERS.  
 SURFACE FINISH:  
 TOLERANCES:  
 $L \leq 4 = \pm 0.1$   $4 < L \leq 15 = \pm 0.2$   
 $15 < L \leq 50 = \pm 0.3$   $50 < L \leq 100 = \pm 0.4$

| NAME                 | DATE       |
|----------------------|------------|
| DRAWN MARTIN ELLIOTT | 08/08/2013 |
| CHK'D                |            |
| APP'VD               |            |

MATERIAL  
 PA66 UL94 V2

HEAT TREATMENT  
 N/A

FINISH  
 NATURAL

TITLE  
 DUAL LOCKING CIRCUIT  
 BOARD SUPPORT

CUSTOMER PART NO.

DWG NO.  
 TRMDLSP1-XXM-01

A3