

CUSTOMER PRINT

PART NUMBER: CA16280XSXXX84

- NOTES:
- 1. FINISHED CABLE ASSEMBLY TO BE COILED
 - 2. OVERMOLD BOOT MATERIAL: PVC, BLACK
 - 3. ELECTRICAL TEST: 100% CONTINUITY
 - 4. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHEN NOTED WITH TOLERANCE

ASS'Y P/N	NO. OF POS.
CA162802SXXX84	2
CA162803SXXX84	3
CA16280XSXXX84	



CABLE LENGTH IN "INCHES"

NO OF POSITIONS

ASS'Y P/N	"X" DIM.
CA162802S03984	3 FT. 3 1/2 IN. ± 2 IN. [1M]
CA162803S03984	
CA162802S07984	6 FT. 7 IN. ± 2 IN. [2M]
CA162803S07984	
CA162802S19784	16 FT. 5 IN. ± 4 IN. [5M]
CA162803S19784	
CA162802S39484	32 FT. 9 3/4 IN. ± 8 IN. [10M]
CA162803S39484	
CA16280XSXXX84	

CABLE LENGTH IN "INCHES"

NO OF POSITIONS



CUSTOMER APPROVAL	
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT / INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.	
APPROVED BY:	_____
DATE:	_____

RoHS COMPLIANT

DIMENSIONS IN BRACKET [] ARE METRIC.

ASSY P/N	CABLE	COLOR CODE END "A"		
CA162802SXXX84	2/20 AWG O.D. 0.215 REF	COLOR CODE		
		POS. 1	POS. 2	
		BLK	WHT	
CA162803SXXX84	3/20 AWG O.D. 0.220 REF	WIRE COLOR CODE		
		POS. 1	POS. 2	POS. 3
		BLK	WHT	GRN

A	AN	03-12-18	DRAWING CREATED PER DOR 17-8167JS	
REV.	INIT.	DATE	DESCRIPTION	
	AN	02-26-18	ORIG. DRAWN BY: DATE: 02-26-18	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			CHECKED BY:	
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			APPROVED BY:	
= CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			TITLE: CABLE ASSEMBLY (2-3) #20 SOCKET CONTACTS MICRO-CON-X, STRAIGHT STANDARD PRODUCT	
FILE: CA16280XSXXX84			PART NUMBER: CA16280XSXXX84	
DIRECTORY: SLW			REV A	