



- NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BRASS PER QQ-B-626
 2. BRASS PER QQ-B-613
 3. NICKEL PL. 100 MIN. THICK OVER ZINC ALLOY
 4. TIN PLATING
 5. PHOSPHOR BRONZE PER QQ-B-750
 6. GOLD FLASH OVER NICKEL PL. 50 MIN. THICK AT MATING AREA.
 7. TIN-LEAD PL. 100 MIN. THICK OVER NICKEL PL. 50 MIN. THICK AT TAIL.
 8. ZINC DIECAST
 9. POLYPROPYLENE UL 94HB

DIMENSIONS ARE IN MILLIMETERS	
UNLESS OTHERWISE SPECIFIED TOLERANCES	
0.5-6	= ±0.2
6-30	= ±0.4
30-120	= ±0.6
120-315	= ±1
315-1000	= ±1.6
1000-2000	= ±2.4

PART NO.	B6251G3-NPP3G-75T
APPROVED	DATE 10-11-01'
CHECKED	DATE 10-11-01'
DRAWN	DATE 10-11-01'
FILE NO.	

Amphenol	
TITLE BNC STRAIGHT PC MOUNT RECEPT. JACK	
DRAWING NO.	
ITEM NO.	

REVISIONS		
ISS	ZONE	DESCRIPTION\PER REQUEST\DATE

NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.
7	HEX NUT		NOTE 1	NOTE 3	
6	LOCK WASHER		NOTE 2	NOTE 3	
5	MOUNTING POST		NOTE 2	NOTE 4	
4	POST	COPPER		NOTE 4	
3	CONTACT PIN		NOTE 5	NOTE 6	
2	INSULATOR		NOTE 8	NATURAL	
1	BODY		NOTE 7	NOTE 3	