









NOTE:


Technical Requirement:The dimension with" * " is for safety standard.

REV.	DESCRIPTION	DESIGN	APPROVAL	DATE
A	NEW	JING LIU	QS LIU	2017.9.27



Marking












X. :±0.6	X.° :±1°	DWG TYPE: PRODUCT DRAWING	Part CA-C13-US-3M 		
.X :±0.4	.X° :±0.6°		TITLE: UL 5-15P Three Pin PLUG		
.XX:±0.10	.XX°:±0.3°	MOULD NO: AC-P0127-x	DWG NO: A12-0127-AC2-1		
UNITS	mm	APPD: 欧阳光仁		SCALE	SHEET
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF LUXSHARE-ICT AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF LUXSHARE-ICT		CHKD: 刘秋顺		NONE	1/1
		DRAW: 刘景			REV. A

1	SVT 18AWGX3C OD:6.1	Round Cable
NO.	SPECIFICATION	Remark


NOTE:


Technical Requirement:The dimension with" * " is for safety standard.

REV.	DESCRIPTION	DESIGN	APPROVAL	DATE
A	NEW	JING LIU	QS LIU	2017.9.27
B	CCC 去掉"S"标志	FG HU	QS LIU	2020.04.16






Marking



X. :±0.6	X.° :±1°	DWG TYPE: PRODUCT DRAWING	Part CA-C13-US-3M 		
.X :±0.4	.X° :±0.6°		TITLE: CCC/VDE/UL C13 Connector		
.XX:±0.10	.XX°:±0.3°	MOUID NO: AC-C0120-x	DWG NO: A12-0120-AC2-5		
UNITS	mm	APPD: 欧阳光仁		SCALE	SHEET
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF LUXSHARE-ICT AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF LUXSHARE-ICT		CHKD: 刘秋顺		NONE	1/1
		DRAW: 胡方刚		REV.	B

1	SVT 18AWG*3C 6.1	Round Cable
NO.	SPECIFICATION	Remark

8		7		6		5		4		3		2		1									
Item				Specification				REV. DESCRIPTION DATE A NEW 2013.07.24															
Construction item				ComponentA																			
E	Conductor	AWG		18#(41/34#)		Environmental Requirement : harmful material and process control, please follow DOC NO "QW-Q-043" 																	
		Material		Bare Copper																			
		Size		41/0.158±0.008BC																			
D	Insulation	Material		PVC																			
		Min AverageThickness		0.38mm																			
		Min at any Point Thickness		0.33mm																			
		O.D.		2.0±0.08 mm																			
		Color		Black,White,Green																			
Layer	Direction		Right (S)																				
	Filler		PP-Tape																				
	Diameter		4.3mmRef																				
WRap	Material		---																				
	Overlap Rate		---																				
	Direction		---																				
C	Jacket	Material		PVC																			
		Diameter		6.1±0.20mm																			
		Min AverageThickness		0.76mm																			
		Min at any Point Thickness		0.69mm																			
		Color		Black																			
		Exrtusion		Solid																			
		Surface		Plane																			
Marking	Marking Color		White																				
	Marking Content		(UL) E325848 SVT VW-1 60℃ 300V 3×0.824mm ² (18AWG).....CSA 246445 SVT FT1 60℃ 300V 3×0.824mm ² (18AWG) ASAP																				
Electric Characters				Physical Characters:										58.37±4% 單重(G/M)									
1.Voltage rating :300V				1.Flame test of cable : VW-1																			
2.Temperature rating :60℃				2.Tensil strength test are before aging :																			
A	3.Spark test : AC-3000V/0.15 sec MIN		> 1.05kgf/mm ² (Insulation,Jacket)		X.± *									X.°±	UNITS	NAME(INTENDED USE)		Part CA-C13-US-3M 					
	4.Dielectric strength : AC-1500V/MIN MIN		3.Tensil strength test are after aging:		.X± *									.X°±	mm	SVT 18#41/0.158BC*3C+F							
	5.Insulation resistance:		> 85%Tensil strength before aging (Insulation,Jacket)		.XX± *									.XX°±	MATL	PART NO.		TITLE: SVT 18#41/0.158BC*3C+F BLACK O.D.:6.1±0.20mm					
	PVC DC-500V 0.762MΩ.KM MIN at 20℃		4.Elongation before aging: >100% (Insulation,Jacket)		.XXX± *									.XXX°±		00A-813200-001R							
	6.Conductor resistance :		5. Elongation after aging:		THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ASAP TECHNOLOGY(JIANGXI)CO., LIMITED AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ASAP TECHNOLOGY(JIANGXI)CO., LIMITED.				APPD: 杨保根		DWG NO: 00A-813200-001R												
	18AWG 22.4Ω/KM MAX at 20℃		> 65%Tensil strength before aging(Insulation)						CHKD: 欧阳光仁														
			> 45%Tensil strength before aging(Jacket)						Q'TY		DR: 刘波		 SCALE SHEET REV. NONE 1/1 A										
8		7		6		5		4		3		2		1									



58.37±4%
單重(G/M)



Part CA-C13-US-3M

NAME(INTENDED USE)
SVT 18#41/0.158BC*3C+F


PART NO.
00A-813200-001R

TITLE: SVT 18#41/0.158BC*3C+F
BLACK O.D.:6.1±0.20mm

APPD: 杨保根

DWG NO:
00A-813200-001R

CHKD: 欧阳光仁



DR: 刘波

SCALE	SHEET	REV.
NONE	1/1	A

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ASAP TECHNOLOGY(JIANGXI)CO., LIMITED AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ASAP TECHNOLOGY(JIANGXI)CO., LIMITED.