




SECTION B-B

UPDATE DRAWING
EC NO: S2008-0663
DRW:KHLIM
CHKD:CGOH
APPR:KCLING
REV
A6

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.20	± ---
1 PLACE	± ---	± ---
ANGULAR ± 3 °		

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY	DATE
DKOH	2004/11/23
CHECKED BY	DATE
KCLING	2004/12/01
APPROVED BY	DATE
SKTOH	2004/12/01
MATERIAL NO.	SEE TABLE

SCALE
NTS

DESIGN UNITS
METRIC

THIRD ANGLE PROJECTION

SERIAL ATTACH SCSI
RECEPTACLE, HYBRID
STANDARD HEIGHT


MOLEX INCORPORATED

DOCUMENT NO.
SD-87839-040


SHEET NO.
2 OF 4

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

10	9	8	7	6	5	4	3	2	1
PART NO	PACKAGING	QUANTITY	HOLD DOWN	PICK AND PLACE CAP	DIM P (16X) (PORT 1 AND POWER PORT) (EXCLUDING P4 AND P12)	DIM Q (2X) (PORT P4 AND P12)	DIM R PCB THICKNESS	DIM S (2X) PEG HEIGHT	DIM T (2X) BLADE/FORKLOCK HEIGHT
87839-0011	TRAY	50/TRAY	BLADE	YES	3.49±0.15	2.99±0.15	3.00±0.10	3.70±0.10	3.12
87839-0019	TRAY	30/TRAY	BLADE	NO	3.49±0.15	2.99±0.15	3.00±0.10	3.70±0.10	3.12
87839-0017	TAPE AND REEL	350/REEL	BLADE	YES	3.49±0.15	2.99±0.15	3.00±0.10	3.70±0.10	3.12
87839-0018	TAPE AND REEL	350/REEL	BLADE	YES	2.36±0.15	2.36±0.15	2.36±0.10	2.00±0.10	2.36
87839-0039	TAPE AND REEL	350/REEL	FORKLOCK	YES	2.11±0.15	2.11±0.15	2.36±0.10	2.00±0.10	2.06




RECOMMENDED PCB LAYOUT
RECOMMENDED PCB THICKNESS DIM R±0.10




UPDATE DRAWING EC NO: S2008-0663 DRW:KHLIM CHKD:GQH APPR:KCLING 2008/02/14 2008/02/15 2008/02/18	QUALITY SYMBOLS ▽=0 ◻=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± ---		DRAWN BY: DKOH CHECKED BY: KCLING APPROVED BY: SKTOH		DATE: 2004/11/23 DATE: 2004/12/01 DATE: 2004/12/01		SERIAL ATTACH SCSI RECEPTACLE, HYBRID STANDARD HEIGHT	
		ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.		MOLEX INCORPORATED	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SD-87839-040	

TRAY PACKAGING



NOTES:

1. PACKAGING QTY: 30PCS/TRAY
2. NO PICK AND PLACE CAP



DETAIL3

-
- Diagram illustrating the peeling direction for the adhesive tape. The tape is shown being peeled at an angle of 15° MAX. The peeling direction is indicated by an arrow pointing upwards and to the left, labeled "PEEL OFF DIRECTION". The pulling out direction is indicated by an arrow pointing to the right, labeled "PULL OUT DIRECTION".

3. PACKAGING QTY IS: 350 PCS/REEL
4. PACKAING STANDARD IS AS PER EIA-481.
5. CONNECTOR COMES WITH PICK AND PLACE CAP.

UPDATE DRAWING EC NO: S2008-0663 2008/02/14 DRAWN:KLM 2008/02/15 CHK'D:CGH 2008/02/18 APPR:KCLING	DESCRIPTION A6	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY DKOH	DATE 2004/11/23	TITLE SERIAL ATTACH SCSI RECEPTACLE, HYBRID STANDARD HEIGHT			
			4 PLACES	± ---	± ---	CHECKED BY KCLING	DATE 2004/12/01				
			3 PLACES	± ---	± ---	APPROVED BY SKTOH	DATE 2004/12/01				
			2 PLACES	± 0.20	± ---			MOLEX INCORPORATED			
			1 PLACE	± ---	± ---			DOCUMENT NO. SD-87839-040			
					ANGULAR ± 3 °		MATERIAL NO.				SHEET NO. 4 OF 4
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE							
				SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					