








END1



VIEWED FROM FRONT



END2



VIEWED FROM FRONT

MOLEX MATERIAL NUMBER	MATERIAL NUMBER REVISION	CUSTOMER PART NUMBER	DIM - 'A' REF	DIM - 'B'	CABLE	END1 CONNECTOR PN	END2 CONNECTOR PN	DATA RATES FOR HBW CABLES
2257722511	A2		621	500 ±10	USB 3.0	100076-6800	100076-6800	-
2257722512	A2		1121	1000 ±10	USB 3.0	100076-6800	100076-6800	-
2257722513	A2		1621	1500 ±15	USB 3.0	100076-6800	100076-6800	-
2257722514	A2		2121	2000 ±15	USB 3.0	100076-6800	100076-6800	-
2257726512	A1		1121	1000 ±10	LVDS 4-PAIR	111149-6924	111149-6924	-
2257726513	A1		1621	1500 ±15	LVDS 4-PAIR	111149-6924	111149-6924	-
2257726514	A1		2121	2000 ±15	LVDS 4-PAIR	111149-6924	111149-6924	-
2257726518	A1		4121	4000 ±25	LVDS 4-PAIR	111149-6924	111149-6924	-
2257725512	A2		1121	1000 ±10	HBW LVDS 2-PAIR	111149-7027	111149-7027	B
2257725513	A2		1621	1500 ±15	HBW LVDS 2-PAIR	111149-7027	111149-7027	B
2257725514	A2		2121	2000 ±15	HBW LVDS 2-PAIR	111149-7027	111149-7027	D
2257725518	A2		4121	4000 ±25	HBW LVDS 2-PAIR	111149-7027	111149-7027	B


SEE NOTE 6.

NOTES:

- A2 1. PRODUCT SPECIFICATION: 2257721200.
2. PACKAGING SPECIFICATION: RPK-100182-0006.
3. PLEASE REFER TO ENGINEERING SPECIFICATION 2093051000 FOR DETAIL LABEL INFORMATION.
ATTENTION: FINAL GOODS LABEL WILL BE PRINTED WITH THE CUSTOMER PART NUMBER MENTIONED ON THE DRAWING.
IF THE CUSTOMER PART NUMBER FIELD IS EMPTY, TBD, NA OR NOTATES ANOTHER PLACEHOLDER INDICATING NO CUSTOMER PART NUMBER IS AVAILABLE THEN THERE WILL BE NO CUSTOMER PART NUMBER PRINTED ON THE LABEL.
LABEL COLOR DEFINITION:
WHITE : MEANS IT IS A PPAP/PRODUCTION PRODUCT.
BLUE : MEANS IT IS A NON-PPAP, PRE-PRODUCTION PART NOT INTENDED FOR SALE-ABLE VEHICLES.
4. VISIT www.molex.com FOR ENVIRONMENTAL COMPLIANCE INFORMATION.
5. SEALED HSAL2 CONNECTORS SHALL BE 100% LEAK TESTED DURING PRODUCTION UNDER TEST PARAMETERS AS DETAILED IN PRODUCT SPECIFICATION PS-34858-001.
6. CABLE BANDWIDTH LETTER AS DEFINED PER 2175470000 PS.

FUNCTIONAL SYMBOLS FA = 0 FC = 0 FP = 0 DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:																				
	DIMENSION UNITS mm	SCALE NTS																					
	GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 797536 DRWN: KMANISHTIWAR CHK'D: SUBHAP2 APPR: ADITHS1		2024/09/09 2024/09/09 2024/09/09		HS2 CABLE ASSY 12CKT PLG TO 12CKT PLG STR POL-A TO STR POL-A																
	ANGULAR TOL ± 3.0°		INITIAL REVISION: DRWN: SAKSHARAD APPR: TSWAROOPNUNE		2024/02/20 2024/03/06																		
4 PLACES ±		3 PLACES ±		2 PLACES ± 0.13		1 PLACE ± 0.25		0 PLACES ±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
												D-SIZE		225772		SEE CHART						1 OF 2	


REVISIONS		
DATE	PSD DOCUMENT REVISION	DESCRIPTION
2024/02/20	A	ORIGINAL RELEASE.
2024/03/13	A1	1. ADDED DATA RATES FOR HBW CABLES. 2. ADDED NOTE 6. 3. UPDATED WIRING DIAGRAM FOR USB 3.0 CABLE.
2024/09/09	A2	UPDATED PS SPEC PN TO 2257721200 WAS PS-34861-001.



CABLE CONSTRUCTION

4-PAIR LVDS


WIRING DIAGRAM FOR 4-PAIR LVDS CABLE					
12CKT (END 1)			12CKT (END 2)		
SIGNAL NAME	CONTACT	WIRE COLORS	WIRE COLORS	CONTACT	SIGNAL NAME
PAIR DRAIN C	1	DRAIN C	DRAIN C	1	PAIR DRAIN C
TPC+	2	NATURAL W/ GREEN STRIPE	NATURAL W/ GREEN STRIPE	2	TPC+
TPC -	3	NATURAL W/ YELLOW STRIPE	NATURAL W/ YELLOW STRIPE	3	TPC -
PAIR DRAIN A	4	DRAIN A	DRAIN A	4	PAIR DRAIN A
TPA +	5	NATURAL	NATURAL	5	TPA +
TPA -	6	NATURAL W/ BLUE STRIPE	NATURAL W/ BLUE STRIPE	6	TPA -
TPD +	7	NATURAL W/ ORANGE STRIPE	NATURAL W/ ORANGE STRIPE	7	TPD +
TPD -	8	NATURAL W/ VIOLET STRIPE	NATURAL W/ VIOLET STRIPE	8	TPD -
PAIR DRAIN D	9	DRAIN D	DRAIN D	9	PAIR DRAIN D
TPB +	10	NATURAL W/ BLACK STRIPE	NATURAL W/ BLACK STRIPE	10	TPB +
TPB -	11	NATURAL W/ RED STRIPE	NATURAL W/ RED STRIPE	11	TPB -
PAIR DRAIN B	12	DRAIN B	DRAIN B	12	PAIR DRAIN B
CABLE BRAID	SHIELD	BRAID TO SHIELD		SHIELD	CABLE BRAID



CABLE CONSTRUCTION

2-PAIR STP HIGH BANDWIDTH 28AWG CABLE

WIRING DIAGRAM FOR HBW LVDS 2-PAIR CABLE					
12CKT (END 1)			12CKT (END 2)		
SIGNAL NAME	CONTACT	WIRE COLORS	WIRE COLORS	CONTACT	SIGNAL NAME
LVDS A DRAIN WIRE	1	DRAIN A	DRAIN A	1	LVDS A DRAIN WIRE
LVDS A SIGNAL (+)	2	NATURAL W/ BLUE STRIPE	NATURAL W/ BLUE STRIPE	2	LVDS A SIGNAL (+)
LVDS A SIGNAL (-)	3	NATURAL	NATURAL	3	LVDS A SIGNAL (-)
LVDS B DRAIN WIRE	4	DRAIN B	DRAIN B	4	LVDS B DRAIN WIRE
LVDS B SIGNAL (+)	5	NATURAL W/ RED STRIPE	NATURAL W/ RED STRIPE	5	LVDS B SIGNAL (+)
LVDS B SIGNAL (-)	6	NATURAL W/ BLACK STRIPE	NATURAL W/ BLACK STRIPE	6	LVDS B SIGNAL (-)
NO CONNECT	7	--	--	7	NO CONNECT
NO CONNECT	8	--	--	8	NO CONNECT
NO CONNECT	9	--	--	9	NO CONNECT
NO CONNECT	10	--	--	10	NO CONNECT
NO CONNECT	11	--	--	11	NO CONNECT
NO CONNECT	12	--	--	12	NO CONNECT
CABLE BRAID	SHIELD	BRAID TO SHIELD		SHIELD	CABLE BRAID



CABLE CONSTRUCTION
USB 3.0 CABLE AWG28/24

WIRING DIAGRAM FOR USB 3.0 CABLE					
12CKT (END 1)			12CKT (END 2)		
SIGNAL NAME	CONTACT #	WIRE COLORS	WIRE COLORS	CONTACT #	SIGNAL NAME
GND_DRAIN TX	1	DRAIN A1	DRAIN A1	1	GND_DRAIN TX
SSTX+	2	YELLOW	YELLOW	2	SSTX+
SSTX-	3	BLUE	BLUE	3	SSTX-
GND_DRAIN RX	4	DRAIN A2	DRAIN A2	4	GND_DRAIN RX
SSRX+	5	ORANGE	ORANGE	5	SSRX+
SSRX-	6	VOILET	VOILET	6	SSRX-
VBUS	7	RED	RED	7	VBUS
NO CONNECT	8	--	--	8	NO CONNECT
D-	9	WHITE	WHITE	9	D-
D+	10	GREEN	GREEN	10	D+
NO CONNECT	11	--	--	11	NO CONNECT
GND	12	BLACK	BLACK	12	GND
BRAID TO SHIELD	SHIELD	BRAID TO SHIELD		SHIELD	BRAID TO SHIELD

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
 = 0  = 0  = 0 DIVISIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex HS2 CABLE ASSY 12CKT PLG TO 12CKT PLG STR POL-A TO STR POL-A										
	mm		NTS															
	GENERAL TOLERANCES (UNLESS SPECIFIED)					EC NO: 797536 DRWN: KMANISHTIWAR 2024/09/09 CHK'D: SUBHAP2 2024/09/09 APPR: ADITHS1 2024/09/09 INITIAL REVISION: DRWN: SAKSHARAD 2024/02/20 APPR: TSWAROOPNUNE 2024/03/06			PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER 2257722511 DOC TYPE PSD DOC PART 000 REVISION A2									
	ANGULAR TOL ± 3.0°																	
	4 PLACES		±															
	3 PLACES		±															
2 PLACES		± 0.13																
1 PLACE		± 0.25		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIRD ANGLE PROJECTION 		DRAWING D-SIZE		SERIES 225772		MATERIAL NUMBER SEE SHEET 1		CUSTOMER		SHEET NUMBER 2 OF 2	
0 PLACES		±																

DOCUMENT STATUS	P1	RELEASE DATE	2024/09/09 12:15:25															MUST REMAIN WITHIN DIMENSIONS			D-SIZE	225772	SEE SHEET 1	2 OF 2
------------------------	----	---------------------	---------------------	--	--	--	--	--	--	--	--	--	--	--	--	--	--	----------------------------------	--	--	--------	--------	-------------	--------

REVISION / DATE 20200914	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1
-----------------------------	----	----	----	----	----	----	----	----	----	----	---	---	---	---	---	---	---	---	---