




PRELIMINARY

THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	I	PRELIMINARY	11SEP2019	T.S	E.I

1 MATERIAL AND FINISH
HOUSING : LIQUID CRYSTAL PLASTIC, BLACK
CONTACT : COPPER ALLOY, PLATING: CONTACT AREA SEE TABLE
SOLDERING AREA TIN
2. INSTRUCTION SHEET: 408-78171



0.38um GOLD	3	22.9	15	24.9	4	2-2336491-4
0.38um GOLD	2	17.9	10	19.9	3	2-2336491-3
TIN	3	22.9	15	24.9	4	2336491-4
TIN	2	17.9	10	19.9	3	2336491-3
CONTACT AREA	D	DIM C	DIM B	DIM A	NO OF	PART NUMBER
PLATING					POSN	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.5
1 PLC ±0.5
2 PLC ±0.5
3 PLC ±
4 PLC ±
ANGLES ±5°

FINISH

DWN H.OSABE 15MAY2019
CHK T.SHIMOYASU 15MAY2019
APVD F.IKEMATSU 15MAY2019

PRODUCT SPEC 108-140223
APPLICATION SPEC -
WEIGHT -

CUSTOMER DRAWING


TE Connectivity

NAME
HEADER ASSEMBLY, 270 DEGREE TYPE
D2970 PUSH-IN TYPE, DYNAMIC
FIELD INSTALLABLE CONNECTOR


SIZE 300779 CAGE CODE 00779 DRAWING NO C-2336491 RESTRICTED TO -

SCALE 1:1 SHEET 1 OF 2 REV 1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.OSABE 15MAY2019		TE Connectivity			
DIMENSIONS: mm		CHK T.SHIMOYASU 15MAY2019					
		APVD F.IKEMATSU 15MAY2019		NAME HEADER ASSEMBLY, 270 DEGREE TYPE D2970 PUSH-IN TYPE, DYNAMIC FIELD INSTALLABLE CONNECTOR			
		PRODUCT SPEC 108-140223					
MATERIAL - -		APPLICATION SPEC - -		SIZE A3	CAGE CODE 00779	DRAWING NO C-2336491	RESTRICTED TO -
FINISH - -		WEIGHT -		CUSTOMER DRAWING			
				SCALE 5:1	SHEET 2 OF 2		REV 1