



USED ON



BLUE

MECHANICAL ENGINEERING

MAR 20 1988

ISSUED BY

### DIE CLOSURE

SEL.	GO	NO-GO
8	.0390	.0440
7	.0340	.0390
6	.0300	.0350
5	.0260	.0310
4	.0220	.0270
3	.0190	.0240
2	.0160	.0210
1	.0130	.0180

CUSTOMER DRAWING  
UNPUBLISHED

601966-1	CRIMPING TOOL, AS SHOWN	ITEM NO
DWG SIZE	PART NO	DESCRIPTION
← REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)		

QTY REQD PER ASSY

### PARTS LIST

		MATERIAL	HEAT TREAT	FINISH
		#	#	#
		TOLERANCES UNLESS OTHERWISE SPECIFIED:	DR. Roy. 6-9-88 CTR. W. Williams 6/12/88 REL. F. HANSEN 3-20-89	
		DECIMALS: .00 = ± .00 .000 = ± .000 .0000 = ± .0000 ANGLES: 20° 20' FRACTIONS: ± 1/64	<b>AMP'S PRODUCTS CORPORATION</b> Valley Forge, PA 19402 A Subsidiary of AMP Incorporated	
		REMOVE BURRS	NAME CRIMPING TOOL	
		SCALE	M22520/2-01	
P	F	LTR	REVISION RECORD	REV
			APP. DATE	SHEET #
			APPROVED	0
			DWG NO	
			601966-1	

THIS INFORMATION IS CONFIDENTIAL AND IS ENCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHERS WITHOUT WRITTEN AUTHORIZATION FROM AMP PRODUCTS CORP., VALLEY FORGE, PA, U. S. A.

DO NOT SCALE DRAWING

58

D

DIST

1