







PART NO.	DESCRIPTION
10178546-102LF	2 POS SMT BOARD CONNECTOR



ARROW MARK
CONNECTOR FRONT SIDE



DINSTACK SMT HDR CONNECTOR WITH PICKUP CAP



NOTES:

- MATERIAL
INSULATOR : HIGH TEMPERATURE THERMOPLASTIC, UL94V-0
CONTACTS : COPPER ALLOY
- PLATING
MATING AREA : 2.54μ (100μin) MATTE Sn OVER Ni
TERMINAL AREA : Sn OVER Ni
- PACKING : TAPE AND REEL
- THIS PRODUCT WITHSTANDS REFLOW TEMPERATURE 260°C FOR 10 SECONDS.
- COPLANARITY : 0.10 MM MAX

spec ref	dr	Nirmal Sam-MB	2024/11/26	projection	MM	size	A3	scale	3:1
tolerance std	eng	Nirmal Sam-MB	2024/11/26	chr	-	ecn no			
ISO 406	appr	Mathew Jacob	2024/11/26	product family	ROTASENSE	rel level	Released		
ISO 1101									
surface	linear	0.X	±	Amphenol FCi	2 POS SMT BOARD CONNECTOR	dwg no	10178546	rev	A
ISO 1302	angular	0°	±°		FOR TEMPERATURE SENSOR CONNECTOR				
				cat. no.		Product - Customer Drw		sheet 1 of 1	