




Additional coding
View in direction A





G60WBM-P09WMMO-0000
Mechanical coding: B
Color coding: red




G60WCM-P09WMM0-0000
Mechanical coding: C
Color coding: blue



G60WDM-P09WMMO-0000
Mechanical coding: D
Color coding: green



G60WAM-P09WMM0-0000
Mechanical coding: A
Color coding: light brown



Technical information

- Max. cable Ø 7.0mm (Based on cable with one braided shield)
- Power solder contacts: AWG 22 (pos.1/2/3/5/6/7)
Current load: 5A (Single contact)

- Signal solder contacts: AWG 28 (pos.4/8/9)
Current load: 1A (Single contact)

Test voltage: 750V (acc. SAE AS 13441:1998, Contact to contact)
Rated voltage: 250V (acc. SAE AS 13441:1998)

1) For crimp information, torque, etc. see assembly instruction 010.650.001.000.006 (www.odu.de/downloads)

2) Maximal operating voltage at sea level up to 2.000 m.
Rated voltage applies no other electrical safety standard. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. This must be evaluated in the frame of equipment engineering.

All shown connectors are according
to DIN EN 61984:2009
connectors without breaking capacity (COC)!

Power	1,2,3,5,6,7
USB (D+ D-)	8,9
Discrete	4

				General tolerances to to DIN ISO 2768-mH				PE-modell-nr.:		
				Toleration to DIN ISO 8015				CAD-nr.:	sheet.:	
				2015	date	name	designation:			scale:
				prep.	14.08.	M. Meier	Receptacle			4:1
				app.						
				norm.						
							drawing nr.:			copy
							G60W.M-P09WMM0-0000			
index	notice	date	name	 A PERFECT ALLIANCE.			replacement for:			nr.