

THIS DRAWING IS UNPUBLISHED.






RELEASED FOR PUBLICATION

© COPYRIGHT copyright.dBye-



ALL RIGHTS RESERVED.

1.MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC
POLYESTER(94V-0),COLOR:BLACK
CONTACT: PRE-TIN COPPER ALLOY
RETENTION LEG:PRE-TIN COPPER ALLOY
2.THE SHARE,SIZE AND POSITION OF THE CHARACTER
SHOW THE OUTLINE. THEY DON'T SHOW DETAIL.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	03DEC2020	F.Z	R.B



RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1



20POS: 1-2379284-0

10POS: 1-2379284-5

20	X	9	18.0	21.0	22.6	PRE-TIN	1-2379284-0
10	X	4	8.0	11.0	12.6	PRE-TIN	1-2379284-5
POS.	KEY	n	A	B	C	FINISHED	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
±0.3, ±3°

0-PLC	±
1-PLC	±0.3
2-PLC	±0.10
3-PLC	±0.001
4-PLC	±0.0001

MATERIAL

APVD
FISHER, ZHU
CHK
RICK, BIAN
RICK, BIAN

PRODUCT SPEC
108-78298
108-137366

APPLICATION SPEC
114-5377

WEIGHT

CUSTOMER DRAWING

04-Dec-20
04-Dec-20
04-Dec-20

NAME
DYNAMIC D1100D 2.0mmPITCH
HDR ASSY, H-TYPE PRE-TIN
4-20POS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2379284	

SCALE	SHEET	OF	REV
6:1	1	1	A

TE Connectivity