








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	15NOV2019	DW	CW
	A1	ECR-20-008707	29JUN2020	DW	CW



- NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 30V
RATED CURRENT: 1.2A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 1.5KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
TEMPERATURE RANGE: -20~+125°C
WIRE RANGE: FOR 210 DATE: 0.14~1.0 mm² (26~18 AWG)
FOR 606 DATE: 0.08~0.34 mm² (28~22 AWG)
CONTACT TYPE: CRIMP CONTACT
2. DATA ELEMENT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO PARTS:
FOR 210 DATE: 40.A722.00 + 61.253.11;
FOR 606 DATE: 40.A703.00 + 61.252.11)

- 注释:
1. 技术参数:
绝缘材料: PC
额定电压: 30V
额定电流: 1.2A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 1.5KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
温度范围: -20~+125°C
接线范围: 210数据传输模块: 0.14~1.0 mm² (26~18 AWG)
606数据传输模块: 0.08~0.34 mm² (28~22 AWG)
接线类型: 冷压接
2. 数据传输模块需要单独订购.
(订货号参考: 210数据传输模块: 40.A722.00 + 61.253.11
606数据传输模块: 40.A703.00 + 61.252.11)

T2115032101-000	HMN-D3-2/6-M	HMN-D3-2/6 MALE MODULE INSERT HMN-D3-2/6 模块公插			
PART NUMBER 料 号		PART DESCRIPTION 描 述			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID WANG 12JUL2019	 TE Connectivity					
		CHK GINO YAO 12JUL2019						
DIMENSIONS: mm		APVD CHRIS WANG 12JUL2019	NAME HMN-D3-2/6-M					
		PRODUCT SPEC 108-137419	SIZE A3					
		APPLICATION SPEC 114-137419					CAGE CODE 00779	
		DRAWING NO C-T2115032101000						
MATERIAL - -		FINISH - -	RESTRICTED TO					
		WEIGHT -						
		RESTRICTED CUSTOMER		SCALE 3:2	SHEET 1 OF 1	REV A1		