




P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O. PI7330	08FEB2001	-	RDR
	A	REVISED PER E.O. PI7424	02JAN2002	-	RDR
	A1	REVISED PER PCN E-20-013840	18SEP2020	MK	IG
	A2	REVISED PER ECR-21-005465	14MAY2021	EC	IG



5. THIS PART MATES WITH HDP26-18-6S*-****.
(****= ALL MODIFICATIONS, *= TYPE OF SEAL.)

4. FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS
SEE ENVELOPE DWG. 0425-015-0000 AND 0425-021-0000.

3. RECOMMENDED PANEL THICKNESS: .062[1.58] TO .187[4.76].


2. THIS CONNECTOR WILL ACCOMMODATE THE FOLLOWING WIRE INSULATION DIAMETERS.

SEAL TYPE	CONTACT SIZE	MIN INSULATION O.D.	MAX INSULATION O.D.	WIRE GAUGE AWG [mm ²] RANGE
N	16	.100 [2.54]	.135 [3.40]	14-20 [2.0-0.5mm ²]
E	16	.053 [1.35]	.120 [3.05]	14-20 [2.0-0.5mm ²]
N OR E	4	.261 [6.63]	.292 [7.42]	6 [13mm ²]

1. THIS RECEPTACLE TO BE USED WITH 114020-90 (ALUMINUM) OR 2411-002-1805 (PLASTIC) PANEL NUT AND 2414-002-1886 LOCKWASHER. PLASTIC PANEL NUT IS PREFERRED.

7 DATE CODE: IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY.
YEAR: FIRST AND SECOND DIGITS. (14=2014)
MONTH: THIRD DIGIT, EXCLUDING 1.A=JAN., B=FEB., C=MARCH...(K=OCT.)
DAY: FOURTH AND FIFTH DIGIT (14=14th DAY)
HOUR: SIXTH AND SEVENTH DIGIT (11=11AM)WHEN * = N: NORMAL SEAL

6 WHEN * = N: NORMAL SEAL.
WHEN * = E: REDUCED DIAMETER SEAL.



RECOMMENDED MOUNTING HOLE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN X. SANCHEZ 27JUN2001	TE TE Connectivity	
		CHK J. APOSTOL 31JAN2002		
DIMENSIONS: INCH [MM]		APVD S. BEARD 31JAN2002	NAME RECEPTACLE CONNECTOR 18-6 ARRANGEMENT HDP20 SERIES	
		PRODUCT SPEC 108-151015	SIZE A3	
		APPLICATION SPEC 114-151015	CAGE CODE 00779	
MATERIAL -		WEIGHT 36.6 g	DRAWING NO. C-HDP24-18-6PX	
FINISH -		CUSTOMER DRAWING	RESTRICTED TO -	
		SCALE 2.000	SHEET 1 OF 1 REV A2	