





COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY.
AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.



FUxx*)P7-K121

e.g. FU25P7-K121

*) xx No. of contacts 09, 15, 25 or 37

MATERIAL NUMBER	xx *)	A [mm]	B [mm]	C [mm]
1731090535	09	30.8	16.9	25
1731090804	15	39.1	25.2	33.3
1731090803	25	53	38.9	47.04
-	37	69.3	55.3	63.5

Crimp contacts FK20P (AWG 20-24/1.3µm Au) included in delivery

3	1	Shell	Steel	tin plated
2	1	Insulator rear part	PEI (-55°C to +130°C)	green
1	1	Insulator front part	PBT acc. UL94V-0	green
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

FUNCTIONAL SYMBOLS ▽ = 0 ▽ = 0 ▽ = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
	DIMENSION UNITS mm		SCALE 2:1	MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-mK		molex	
			CURRENT REVISION				
			DRWN: DRAWN BY msteinbrueck 12-02-2024				
			APPR: APPR BY mteubel 20-02-2024		FCT D-Sub Crimp Connector		
	3 24410		INITIAL REVISION				
	2 24130		DRWN: DRAWN BY MTeubel 14-12-2016				
	1		APPR: APPR BY sschref 14-12-2016		PRODUCT CUSTOMER DRAWING		
	REV. CH.-NO.				MATERIAL NUMBER		
	REPLACEMENT FOR: 1731090535_Rev. A		FRIST ANGLE PROJECTION 		DRAWING A3-SIZE		
				DOCUMENT NUMBER FUxxP7-K121			
				CUSTOMER GENERAL MARKET			
				SHEET NUMBER 1 OF 1			