



SECTION A-A

NOTES:

1. ELECTROLESS NICKEL PLATE PER AMPHENOL SPEC. 949-1012, CLASS 1, GRADE F.
2. PART MUST MEET RoHS SPECIFICATION PER AMPHENOL PROCEDURE 949-1604.

UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE

LINEAR	ANGULAR
X.X ± .02	X° ± 1°
X.XX ± 0.015	X'X' ± 30'
X.XXX ± 0.005	X'X'X' ± 15'

BREAK ALL SHARP EDGES AND REMOVE ALL BURRS

DO NOT SCALE

DIMENSIONS IN INCHES

NOTICE - These drawings, specifications, or other data (1) are remain the property of Amphenol Corporation, (2) must be returned upon request; and (3) are confidential and are not to be disclosed to any person other than those to whom they are given by Amphenol Corporation, or by any other person to anyone for any purpose. It is not to be regarded by implication or otherwise as in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any products, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications or other data.

MATL: BRASS C38000 OR EQUIV

FINISH: SEE NOTE 1

REF.:

DRN: S. LEE

CKD: R. ESSERT

APVD: D. BERGMAN

DATE: 4/07/86

DATE: 6/06/86

DATE: 6/05/86

TITLE:

HEX NUT

REV.	DESCRIPTION	APVD	DATE	ECO No
C	MATERIAL WAS BRASS, ADD "C38000 OR EQUIV" TO MATERIAL; ADD NEW BORDER; ADD NOTE 2	SLS	5/10/06	56-06
B	CHANGED PLATING SPEC.	SCC	5/01/89	21-89
A	FIRST ISSUE	DJB	6/11/86	

**Amphenol**  
FIBER OPTIC PRODUCTS

2100 Western Court, Suite 300, Little, IL 60452, USA

DRAWING NO. **905-5087** SHEET 1 OF 1

THIRD ANGLE PROJECTION

SCALE: 8:1

PART No: **905-5087**

SIZE: B